




- Notes 1 Applicable crimp contact:  
Contact No. 1.3 to 10  
RP17-PC-222/CL113-0508-0  
(Applicable cable size : awg#24 to #28.  
Cable jacket outer diameter shall be  $\phi 1.2\text{mm}$  or less.)  
Contact No. 2, 11, 12  
RP17-PC-212/CL113-0507-7  
(Applicable cable size : awg#18 to #22.  
Cable jacket outer diameter shall be  $\phi 1.7\text{mm}$  or less.)
- 2 Applicable cable crimping tool :  
RP17-TC-01/CL150-0042-5
- 3 Extraction tool : RP6-SC-TP/CL150-0039-0
- ① ④ The tightening torque of Ref No. ⑦ : 0.15 to 0.2 N·m.  
To prevent loosening Ref No. ⑦ , use LOCTITE 243,  
HENKEL JAPAN or equivalent.
- 5 Shall be disassembled when delivered.
- 6 The cable pull and twisting strength and other  
characteristics may differ,  
depending on the cable structure, please confirm  
before the use.

|    |               |                 |    |                    |                                                                      |
|----|---------------|-----------------|----|--------------------|----------------------------------------------------------------------|
| 4  | Brass         |                 |    |                    |                                                                      |
| 3  | Polycarbonate | (Black) UL94V-0 | 7  | Brass              | Black chromete treatment<br>(Trivalent chromium) JIS B 1111 M2X0.4X4 |
| 2  | Polycarbonate | (Black) UL94V-0 | 6  | Steel              | Nickel plating                                                       |
| 1  | Polycarbonate | (Black) UL94V-0 | 5  | Polyvinyl chloride | (Black)                                                              |
| 部番 | 材 質           | 処 理, 備 考        | 部番 | 材 質                | 処 理, 備 考                                                             |

|                                 |  |                |                  |            |                           |          |
|---------------------------------|--|----------------|------------------|------------|---------------------------|----------|
| UNITS<br>mm                     |  | SCALE<br>2 : 1 | 訂 正 記 事          | 設 計        | 検 図                       | 年 月 日    |
|                                 |  | △の数<br>① 2     | DIS-C-00009784   | TY. SUZUKI | HY. KOBAYASHI             | 20220214 |
| HIROSE<br>ELECTRIC<br>CO., LTD. |  |                | 承 認 : MO. SATOH  | 20060630   | 図 番 : EDC-010235-71-71    |          |
|                                 |  |                | 検 図 : MO. SATOH  | 20060630   | 製 品 名 : RP17-13P-12PC(71) |          |
|                                 |  |                | 設 計 : EM. YUMINO | 20060630   | 製 品                       |          |
|                                 |  |                | 製 図 : MM. ISHII  | 20060614   | コード CL0113-0501-0-71      |          |