




- Notes 1 Applicable crimp contact:
Contact No. 1, 3 to 10
RP17-SC-222/CL113-0510-1 (Applicable cable size : awg#24 to #28.
Cable jacket outer diameter shall be $\phi 1.2\text{mm}$ or less.)
Contact No. 2, 11, 12
RP17-PC-212/CL113-0509-2 (Applicable cable size : awg#18 to #22.
Cable jacket outer diameter shall be $\phi 1.7\text{mm}$ or less.)
2 Applicable cable crimping tool : RP17-TC-01/CL150-0042-5
3 Extraction tool : RP6-SC-TP/CL150-0039-0
4 The tightening torque of Ref. No. ⑥ : 0.15 to 0.5 N · m.
To prevent loosening Ref. No. ⑥ , use LOCTITE 243, HENKEL JAPAN or equivalent.
5 Shall be disassembled when delivered.
6 The cable pull and twisting strength and other characteristics may differ,
depending on the cable structure, please confirm before the use.

3	Polycarbonate	(BLACK) UL94V-0	6	Brass	Black chromete treatment (Trivalent chromium) JIS B 1111 M2X0.4X4
2	Polycarbonate	(BLACK) UL94V-0	5	Polyvinylchloride	(BLACK)
1	Polycarbonate	(BLACK) UL94V-0	4	Brass	
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 2 : 1	COUNT 1	DESCRIPTION OF REVISIONS DIS-C-00009784	DESIGNED TY. SUZUKI
HIROSE ELECTRIC CO., LTD.		APPROVED : EJ. KUNII	20160212	DRAWING NO.	EDC-026436-71-00
		CHECKED : EJ. KUNII	20160212	PART NO.	RP17-13J-12SC(71)
		DESIGNED : WR. AJIRO	20160212	CODE NO.	CL0113-0515-5-71
		DRAWN : WR. AJIRO	20160212		