


Sep. 1. 2021 Copyright 2021 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- Notes
- 1 Applicable crimp contact:
 Contact No. 1 to 11 : RP19-PC-222(CL113-0264-7)
 (Wire range, AWG #24 to 28)
 Contact NO. 12 to 13 : RP19-PC-212(CL113-0263-4)
 (Wire range, AWG #18 TO 22)
 - 2 Applicable crimp contact crimping tool: RP13A-TC-01(CL150-0070-0)
 Applicable crimp contact extraction tool: RP6-SC-TP(CL150-0039-0)
 - 3 The recommended clamp torque of Ref.No. ⑥ to 0.2 N·m.
 - 4 This product is delivered disassembled.
 - 5 The cable clamp strength, rotation strength and other
 Please confirm before the use.

4	BRASS		8	Stainless steel	
3	POLYCARBONATE	(BLACK) UL94V-0	7	Flexible polyvinylchloride	(BLACK) UL94V-0
2	POLYCARBONATE	(BLACK) UL94V-0	6	BRASS	ZINC PLATING BLACK CHROMETE TREATMENT (TRIVALENT CHROMIUM) JIS B 1111 M2X0.4X4
1	POLYCARBONATE	(BLACK) UL94V-0	5	STEEL	NICKEL PLATING
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS

UNITS mm		SCALE 2 : 1	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
HIROSE ELECTRIC CO., LTD.		APPROVED	·EJ. KUNII	16. 03. 23	DRAWING NO. EDC-027897-71-00		
		CHECKED	·EJ. KUNII	16. 03. 23	PART NO. RP13A-12PA-13PC(71)		
		DESIGNED	·MM. ISHII	16. 03. 23	CODE NO. CL113-4003-5-71		
		DRAWN	·MM. ISHII	16. 03. 23	1/1		