



Apr.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- NOTES
- THE RECOMMENDED CLAMP TORQUE REF. NO. ⑥ : 5 TO 5.5 N · m.
 - ACROSS FLATS OF HEAGON SOCKET OF REF. NO. ⑩ : 1.27
THE RECOMMENDED CLAMP TORQUE REF. NO. ⑩ : 0.2 TO 0.25 N · m.
 - LOCTITE 263, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO PREVENT
REF. NO. ① AND NO. ⑩ FROM LOOSENING.
 - POSITIONAL RELATIONSHIP IN ROTATIONAL DIRECTION BETWEEN REF. NO. ① AND ⑥ SHOWS AN EXAMPLE.
 - THIS PRODUCT TO BE USED WITH CABLECLAMP, JR25WCC-**,
** DESIGNATE DIAMETER OF APPLICABLE.
 - THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER.
DEPENDING ON THE CABLE STRUCTURE.
PLEASE CONFIRM BEFORE THE USE.

5	PHOSPHOR BRONZE	NICKEL PLATING	10	STAINLESS STEEL								
4	PHENOL-FORMALDEHYDE	(BLACK) UL94V-0	9	ACRYLONITRILE BUTADIENE RUBBER	(GRAY)							
3	PHENOL-FORMALDEHYDE	(BLACK) UL94V-0	8	ACRYLONITRILE BUTADIENE RUBBER	(GRAY)							
2	COPPER ALLOY	SILVER PLATING 2μm min.	7	BRASS	BLACK CHROME PLATING							
1	ALUMINUM ALLOY	BLACK CHROME PLATING	6	BRASS	BLACK CHROME PLATING							
NO.	MATERIAL	FINISH , REMARKS		NO.	MATERIAL	FINISH , REMARKS						
UNITS mm				SCALE 2 : 1	COUNT 	DESCRIPTION OF REVISIONS		DESIGNED	CHECKED	DATE		
 HIROSE ELECTRIC CO., LTD.		APPROVED		+HY. KOBAYASHI		18.02.26		DRAWING NO.			EDC-110575-31-00	
		CHECKED		+HY. KOBAYASHI		18.02.26		PART NO.			JR25WP-16S(31)	
		DESIGNED		+TH. KAMEYA		18.02.23		CODE NO.			CL114-2021-2-31	
		DRAWN		+MK. INOUE		18.02.23					 1/	