






May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- NOTES
- 1 The recommended tightening torque of Ref No. ⑥ : 2 to 2.5 N·m.
 - 2 The recommended tightening torque of Ref No. ⑩ : 0.2 to 0.25 N·m.
 - 3 One example of the rotation of REF. No. ⑥ to REF. No. ① is shown.
 - 4 LOCTITE 263 HENKEL JAPAN or equivalent is recommended to prevent REF. No. ①, ⑥ and ⑩ for loosing.
 - 5 This products to be used with cable clamp, JR16WCC-※
※Designate diameter(mm) of applicable cable.
 - 6 The cable pull and twisting strength, waterproof tightness and other characteristics may differ, depending on the cable structure.
Please confirm before the use.

5	PHOSPHOR BRONZE	NICKEL PLATING	10	STAINLESS STEEL	HEX SOCKET SET SCREW HEX : 1.27					
4	PHENOL FORMALDEHYDE	(BLACK) UL94V-0	9	ACRYLONITRILE BUTADIENE RUBBER	(BLACK)					
3	PHENOL FORMALDEHYDE	(BLACK) UL94V-0	8	ACRYLONITRILE BUTADIENE RUBBER	(BLACK)					
2	COPPER ALLOY	SILVER PLATING 2μm min	7	BRASS	BLACK CHROME PLATING					
1	ALUMINUM ALLOY	BLACK CHROME PLATING	6	BRASS	BLACK CHROME PLATING					
NO.	MATERIAL	FINISH . REMARKS		NO.	MATERIAL	FINISH . REMARKS				
UNITS mm				SCALE 2 : 1		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
 HIROSE ELECTRIC CO., LTD.		APPROVED : HY. KOBAYASHI		18.02.26		DRAWING NO.		EDC-110483-31-00		
		CHECKED : HY. KOBAYASHI		18.02.26		PART NO.		JR16WP-10S(31)		
		DESIGNED : TH. KAMEYA		18.02.23		CODE NO.		CL114-2015-0-31		
		DRAWN : MK. INOUE		18.02.23				 1/		