

APPLICABLE STANDARD																	
RATING	OPERATING TEMPERATURE RANGE	-25 °C TO +85 °C		STORAGE TEMPERATURE RANGE	-10 °C TO +60 °C												
	VOLTAGE																
	CURRENT			APPLICABLE CABLE	φ9±0.5mm												
SPECIFICATIONS																	
ITEM		TEST METHOD		REQUIREMENTS		QT	AT										
CONSTRUCTION																	
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.		X	X										
MARKING		CONFIRMED VISUALLY.				-	-										
ENVIRONMENTAL CHARACTERISTICS																	
CORROSION SALT MIST		EXPOSED IN 5 % SALT WATER SPRAY FOR 500 h.		NO HEAVY CORROSIN RUIN THE FUNCTION.		X	-										
SEALING (1)		EXPOSED AT A DEPTH OF 1.8 m FOR 48 h.		NO WATER PENETRATION INSIDE CONNECTOR.		X	-										
AIRTIGHTNESS(1)		APPLY AIR PRESSURE 18 kPa FOR 0.5min TO INSIDE CONNECTOR.		NO AIR BUBBLES INSIDE CONNECTOR.		X	-										
REVISIONS <table><thead><tr><th>COUNT</th><th>DESCRIPTION OF REVISIONS</th><th>DESIGNED</th><th>CHECKED</th><th>DATE</th></tr></thead><tbody><tr><td>Δ</td><td></td><td></td><td></td><td></td></tr></tbody></table>								COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE	Δ				
COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE													
Δ																	
REMARK NOTE(1) SEALING AND AIRTIGHTNESS SHALL BE TESTED BY APPLICABLE CONNECTOR AND CABLE. Unless otherwise specified, refer to JIS C 5402.(IEC 60512)				APPROVED	HY. KOBAYASHI	18.02.26											
				CHECKED	HY. KOBAYASHI	18.02.26											
				DESIGNED	TH. KAMEYA	18.02.23											
				DRAWN	MK. INOUE	18.02.13											
Note QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.		ELC-110599-31-00													
		SPECIFICATION SHEET		PART NO.	JR13WCC-9 (31)												
		HIROSE ELECTRIC CO., LTD.		CODE NO.	CL114-2050-0-31		1/1										