


Apr.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- NOTES
- 1 ACROSS FLATS OF HEXAGON SOCKET OF REF. NO. ⑭ : 1.27.
THE RECOMMENDED CLAMP TORQUE OF REF. NO. ⑭ : 0.3 TO 0.4N · m.
 - 2 THE RECOMMENDED CLAMP TORQUE OF REF. NO. ⑨ AND NO. ⑬ : 2N · m.
 - 3 LOCTITE 242, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO
PREVENT REF. NO. ⑬ AND NO. ⑭ FROM LOOSENING.
 - 4 ROTATION EXAMPLES OF REF. NO. ① , ⑨ AND ⑬ ARE SHOWN.
 - 5 THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER,
DEPENDING ON THE CABLE STRUCTURE.
PLEASE CONFIRM BEFORE THE USE.

8	PHOSPHOR BRONZE	NICKEL PLATING			
7	STEEL	NICKEL PLATING	15	ACRYLONITRILE BUTADIENE RUBBER	(BLACK)
6	BRASS	NICKEL PLATING	14	STEEL	NICKEL PLATING M2.6x0.45
5	SILICONE RUBBER	(BLACK)	13	BRASS	NICKEL PLATING
4	BERYLLIUM COPPER	SILVER PLATING 2μm min	12	BRASS	NICKEL PLATING
3	BERYLLIUM COPPER	SILVER PLATING 2μm min	11	SILICONE RUBBER	(BLACK)
2	POLYBUTYLENE TEREPHTHALATE	(BLACK) UL94V-0	10	SILICONE RUBBER	(BLACK)
1	ZINC ALLOY	NICKEL PLATING	9	BRASS	NICKEL PLATING
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
UNITS mm		SCALE 2 : 1	COUNT △	DESCRIPTION OF REVISIONS	
HRS HIROSE ELECTRIC CO., LTD.		APPROVED : SU. OBARA	10.10.15	DRAWING NO.	EDC3-044335-73
		CHECKED : HY. KISHI	10.10.14	PART NO.	HR22-12WTPA-20S(73)
		DESIGNED : WR. AJIRO	10.10.14	CODE NO.	CL122-0015-3-73
		DRAWN : WR. AJIRO	10.10.14		
		DESIGNED	CHECKED	DATE	