









NOTES 1. APPLICABLE CRIMPING TERMINAL:

PART NO.	APPLICABLE WIRE SIZE	PLATED TYPE OF CONTACT PORTION
HR31-SC-113	1.04~2.63mm ²	TIN-LEAD PLATING
HR31-SC-123	0.2~1.65mm ²	TIN-LEAD PLATING
HR31-SC-111	1.04~2.63mm ²	GOLD PLATING
HR31-SC-121	0.2~1.65mm ²	GOLD PLATING

2. APPLICABLE CRIMPING TOOL:HR31-TC-01

3. APPLICABLE CRIMPING TERMINAL WITHDRAWAL TOOL:HR31-SC-TP

4. RECOMMENDED CLAMP TORQUE OF REF.NO.3:0.2± 0.02Nm

2	POLYBUTYLENE TEREPHTHALATE	(GREEN)	UL94V-0					
1	POLYBUTYLENE TEREPHTHALATE	(GREEN)	UL94V-0	3	STEEL	NICKEL PLATING		
NO.	MATERIAL	FINISH , REMARKS		NO.	MATERIAL	FINISH , REMARKS		
UNITS mm		SCALE 2 : 1		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
 HIROSE ELECTRIC CO., LTD.		APPROVED	±EJ. KUNII	16.02.17	DRAWING NO.	EDC-112083-72-00		
		CHECKED	±EJ. KUNII	16.02.17	PART NO.	HR31-5.08P-5SC(72)		
		DESIGNED	±SJ. SHIMIZU	16.02.17	CODE NO.	CL131-0002-2-72		
		DRAWN	±SJ. SHIMIZU	16.02.17				
							1	1