



Apr.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

FIGURE-2 (1:1)



- NOTES
- 1 PLATING(REF.NO.0)  
CONTACT AREA : GOLD 0.2μm min  
TERMINAL AREA:GOLD FLACH  
UNDER PLATING : NICKEL 2μm min
  - 2 THE RECOMMENDED CLAMP TORQUE OF REF.NO.0 TO BE 1 TO 1.5N·m.  
APPLY LOCTITE 263 HENKEL JAPAN OR EQUIVALENT TO THE THREADED PORTION OF REF.NO.0 IN ORDER TO PREVENT LOOSENING.
  - 3 THE RECOMMENDED CLAMP TORQUE OF REF.NO.0 TO BE 0.8 TO 1N·m.  
APPLY LOCTITE 263 + LOCK PRIMER 7649 HENKEL JAPAN OR EQUIVALENT TO THE THREADED PORTION (M10X0.75) OF REF.NO.0 IN ORDER TO PREVENT LOOSENING.
  - 4 FASTEN REF.NO.0 TO THE CABLE WITH THE CABLE CRIMPING TOOL.  
AND MAKE REF.NO.0 CONTACT WITH REF.NO.0(REFER TO Fig.1).  
REFER TO THE TECHNICAL SPECIFICATION ETAD-C0099 FOR DETAILS.  
APPLICABLE CABLE CRIMPING TOOL : HR10A-TC-02(CL150-0041-2)(THE HOLE DIAMETER FOR CRIMPING:φ5.3)
  - 5 Fig.2 SHOWS THE APPEARANCE AFTER ASSEMBLY.
  - 6 APPLICABLE CABLE ASSEMBLY FIXTURE : LF07BP-T01(CL150-0232-0)  
CABLE ASSEMBLY FIXTURE IS USED AS A RECEPTACLE STAND OF EXTRACT  
AND THE PART No.0 OF AN ASSEMBLY.
  - 7 ROTATION EXAMPLES OF No.0, 0 AND 0 TO 0 ARE SHOWN.
  - 8 THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER,  
DEPENDING ON THE CABLE STRUCTURE.  
PLEASE CONFIRM BEFORE THE USE.
  - 9 THIS PRODUCT MAY BE STAINED DUE TO LUBRICANT.  
HOWEVER, THIS DOES NOT AFFECT THE PRODUCT PERFORMANCE, SO PLEASE USE IT AS IT IS.

FIGURE-1 (2:1)



|                           |                    |                        |          |                          |                         |
|---------------------------|--------------------|------------------------|----------|--------------------------|-------------------------|
| 7                         | ZINIC ALLOY        | BLACK CHROME PLATING   | 14       | STAINLESS STEEL          |                         |
| 6                         | CHLOROPRENE RUBBER | (BLACK)                | 13       | BRASS                    | NICKEL PLATING          |
| 5                         | STAINLESS STEEL    |                        | 12       | PPS                      | (NATURAL BROWN) UL94V-0 |
| 4                         | ZINIC ALLOY        | BLACK CHROME PLATING   | 11       | POLYAMIDE                | (NATURAL MILKY) UL94V-0 |
| 3                         | PHOSPHOR BRONZE    | 1                      | 10       | CHLOROPRENE RUBBER       | (BLACK)                 |
| 2                         | PPS                | (BLACK) UL94V-0        | 9        | PHOSPHOR BRONZE          | NICKEL PLATING          |
| 1                         | ZINIC ALLOY        | BLACK CHROME PLATING   | 8        | CHLOROPRENE RUBBER       | (BLACK)                 |
| NO.                       | MATERIAL           | FINISH . REMARKS       | NO.      | MATERIAL                 | FINISH . REMARKS        |
| UNITS<br>mm               |                    | SCALE<br>4 : 1         | COUNT    | DESCRIPTION OF REVISIONS | DESIGNED                |
| HRS                       |                    | APPROVED : TP. KOMATSU | 20231227 | DRAWING NO.              | EDC-117383-33-00        |
| HIROSE ELECTRIC CO., LTD. |                    | CHECKED : E.J. KUNII   | 20231227 | PART NO.                 | LF07WBPD-6S(33)         |
|                           |                    | DESIGNED : MK. WADA    | 20231227 | CODE NO.                 | CL0136-0020-6-33        |
|                           |                    | DRAWN : MK. WADA       | 20231227 |                          |                         |