

APPLICABLE STANDARD		2 TÜV approved(R50079865),UL approved(E52653)					
RATING	OPERATING TEMPERATURE RANGE	1 -40 °C TO +85 °C		STORAGE TEMPERATURE RANGE	-10 °C TO +60 °C		
	VOLTAGE	AC 125 V , DC 125 V		WIRE SIZE	MAX AWG#16		
	CURRENT	10 A		APPLICABLE CABLE			
SPECIFICATIONS							
ITEM		TEST METHOD		REQUIREMENTS		QT	AT
CONSTRUCTION							
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.		X	X
MARKING		CONFIRMED VISUALLY.				X	X
ELECTRIC CHARACTERISTICS							
CONTACT RESISTANCE		CONTACT SHALL BE MEASURED AT DC 1 A		5 mΩ MAX.		X	X
INSULATION RESISTANCE		500 V DC.		1000 MΩ MIN.		X	X
VOLTAGE PROOF		1250 V AC. FOR 1 min.		NO FLASHOVER OR BREAKDOWN.		X	X
MECHANICAL CHARACTERISTICS							
CONTACT INSERTION AND WITHDRAWAL FORCES		BY STEEL GAUGE.		INSERTION AND WITHDRAWAL FORCES : — N MIN.		—	—
CONNECTOR INSERTION AND WITHDRAWAL FORCES		MEASURED BY APPLICABLE CONNECTOR.		INSERTION AND WITHDRAWAL FORCES LOCKING DEVICE WITH UNLOCK : 70 N MAX. LOCKING DEVICE WITH LOCK : — N MAX.		X	—
MECHANICAL OPERATION		1000 TIMES INSERTIONS AND EXTRACTIONS.		CONTACT RESISTANCE: 10 mΩ MAX.		X	—
VIBRATION		FREQUENCY: 10 → 55 → 10 (Hz) (1CYC,5min), SINGLE AMPLITUDE 0.75 mm, AT 10 CYC,FOR 3 DIRECTIONS.		①NO ELECTRICAL DISCONTINUITY OF 10 μs. ②NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.		X	—
SHOCK		IN OPPOSITE DIRECTIONS OF EACH 3 DEMENSION AXIS FOR 3 TIMES AT 490 m/s <sup>2</sup> DURATIONS OF PULSE 11 ms.		① NO ELECTRICAL DISCONTINUITY OF 10 μs. ② NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.		X	—
BREAKING STRENGTH		MAX 100 N SHALL BE APPLIED TO CABLE IN UP AND DOWN,LEFT AND RIGHT DIRECTIONS WHEN MATED.		NO BREAKAGE MAX 100N.		X	—
ENVIRONMENTAL CHARACTERISTICS							
DAMP HEAT (STEADY STATE)		EXPOSED AT 40 °C, 90 TO 95 %, 96 h.		① INSULATION RESISTANCE: 10 MΩ MIN (AT HIGH HUMIDITY). ② INSULATION RESISTANCE: 100 MΩ MIN (AT DRY). ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		X	—
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55→ R/T <sup>(1)</sup> → +85 → R/T °C TIME 30 → 2 TO 3 → 30 → 2 TO 3 min UNDER 5 CYCLES.		① INSULATION RESISTANCE: 100 MΩ MIN.. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		X	—
CORROSION SALT MIST		EXPOSED IN 5 % SALT WATER SPRAY FOR 1000 h.		NO HEAVY CORROSION RUIN THE FUNCTION.		X	—
DRY HEAT		EXPOSED AT + 85 °C, 96 h.		NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		X	—
COLD		EXPOSED AT - 55 °C, 96 h.		NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		X	—
RESISTANCE TO SOLDERING HEAT		SOLDER TEMPERATURE, +350±10°C, FOR IMMERSION DURATION, 5±1 s.		NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.		X	—
SOLDERABILITY		SOLDERED AT SOLDER TEMPERATURE, +350±10°C FOR IMMERSION DURATION, 2 TO 3 s.		SOLDER SURFACE TO BE FREE FROM PIN-HOLE, NO WETTING AND OTHER DEFECTS.		X	—
SEALING		EXPOSED AT A DEPTH OF 1.8 m FOR 48 h.		NO WATER PENETRATION INSIDE CONNECTOR.		X	—
AIR TIGHTNESS		APPLY AIR PRESSURE 17.6kPa FOR 0.5min TO INSIDE CONNECTOR.		NO AIR BUBBLES INSIDE CONNECTOR.		X	—
	COUNT	DESCRIPTION OF REVISIONS		DESIGNED	CHECKED	DATE	
2	1	DIS-C-001437		WR. AJIRO	TH. KAMEYA	09.10.17	
REMARK NOTE(1) R/T : ROOM TEMPERATURE  Unless otherwise specified, refer to JIS C 5402.				APPROVED	MO. SATOH	09.01.14	
				CHECKED	HY. KOBAYASHI	09.01.14	
				DESIGNED	TY. SUZUKI	09.01.14	
				DRAWN	TY. SUZUKI	09.01.14	
Note QT:Qualification Test AT:Assurance Test X:Applicable Test				DRAWING NO.		ELC4-114244-03	
HRS	SPECIFICATION SHEET			PART NO.	LF10WBR-4P (03)		
	HIROSE ELECTRIC CO., LTD.			CODE NO.	CL136-1005-8-03	2	1/1