


APPLICABLE STANDARD						
RATING	OPERATING TEMPERATURE RANGE	-40 °C TO +150 °C (1)		STORAGE TEMPERATURE RANGE	-10 °C TO +60 °C	
	VOLTAGE			APPLICABLE CABLE	CONDUCTOR SIZE : 16.78 TO 26.66	
	CURRENT	(3)				
SPECIFICATIONS						
ITEM		TEST METHOD		REQUIREMENTS	QT AT	
CONSTRUCTION						
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	× ×	
ELECTRIC CHARACTERISTICS						
CONTACT RESISTANCE		CONTACT SHALL BE MEASURED AT DC 1 A		0.5 mΩ MAX. (2)	× —	
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE	
0						
REMARK NOTES(1) Operating temperature range includes the temperature rise by current carrying. (2) Contact resistance : Engagement to the receptacle. (3) Rated current is varied depending on each connector used with this contact.Refer to each connector specifications for the rating. Unless otherwise specified, refer to JIS C 5402(IEC 60512).				APPROVED	SU. OBARA	15.05.26
				CHECKED	YH. YAMADA	15.05.26
				DESIGNED	HS. KAWASHIMA	15.05.26
				DRAWN	HR. SATO	15.05.25
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC-117458-02-00	
HRS	SPECIFICATION SHEET		PART NO.	EV1-PC-112 (02)		
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL139-0004-9-02	 1/1	