






Oct.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.




Panel installation hole
Panel thickness(0.7 to 4.5)



PCB layout

(Indicates the side of the surface to which dip posts are inserted.)



- NOTES
- ① Plating (Ref. No. ③, ④)
Contact area : Gold 0.2μm min
Others : Gold flash
Under Plating : Nickel 2μm min
 - ② The recommended clamp torque of Ref.No. ③ to be 1.5 to 2N·m.
Thread locker to the threaded portion of Ref.No. ① is recommended to prevent Ref.No. ④ from loosening. Recommended thread locker:LOCTITE 263,HENKEL JAPAN LTD.
 - ③ When this connector is mounted on to panel,be careful Ref.No. ⑥ is assembled surely into the groove of Ref.No. ① as shown in this figure to keep waterproof effectiveness.
 - ④ Rotation examples of No. ③ and ④ to ① are shown.

4	Phosphor bronze	①	8	Brass	Nickel plating
3	Copper alloy	①	7	Phosphor bronze	Nickel plating
2	PPS	(Black) UL94V-0	6	Chloroprene rubber	(Black)
1	Zinc alloy	Nickel plating	5	Phosphor bronze	Nickel plating
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 4 : 1	COUNT	DESCRIPTION OF REVISIONS	
DESIGNED		CHECKED		DATE	
APPROVED : HY. KOBAYASHI 18.02.22			DRAWING NO. EDC-119204-31-00		
CHECKED : HY. KOBAYASHI 18.02.22			PART NO. LF07WBRB-6SD-A(31)		
DESIGNED : TY. SUZUKI 18.02.22			CODE NO. CL136-1022-0-31		
DRAWN : HM. SAITO 18.02.20			1/1		