







- Notes
- 1 This product is apply to the wire #16 to #20.
(Jacket diameter : $\phi 1.9$ to 3.2mm)
 - 2 Applicable crimping tool : HT802/HR41A-11-16 (CL150-0408-5)(Applicable to AWG#16)
HT802/HR41A-11-18 (CL150-0404-4)(Applicable to AWG#18)
HT802/HR41A-11-20 (CL150-0407-2)(Applicable to AWG#20)
 - 3 Applicable extraction tool : HR41A-TP(CL150-0405-7)
 - 4 Per reel : 100 contacts
 - 5 Contact plating : Gold plating $0.76\mu\text{m}$ min.
 - 1 Terminal plating : Tin plating $0.5\mu\text{m}$ min.
Underplating : Nickel plating $2\mu\text{m}$ min.

1	Copper alloy	5						
NO.	MATERIAL	FINISH . REMARKS		NO.	MATERIAL	FINISH . REMARKS		
UNITS mm		SCALE 10 : 1		COUNT 1	DESCRIPTION OF REVISIONS DIS-C-00000101	DESIGNED HN. TANAKA	CHECKED HY. KISHI	DATE 15. 02. 10
 HIROSE ELECTRIC CO., LTD.		APPROVED	SU. OBARA		14. 05. 16	DRAWING NO. EDC3-118389-00		
		CHECKED	HY. KISHI		14. 05. 16	PART NO. HR41A-PC-111		
		DESIGNED	HN. TANAKA		14. 05. 15	CODE NO. CL141-0214-8-00		
		DRAWN	HN. TANAKA		14. 05. 15			