

APPLICABLE STANDARD						
RATING	OPERATING TEMPERATURE RANGE	-25 °C TO +85 °C		STORAGE TEMPERATURE RANGE	-10 °C TO +60 °C	
	VOLTAGE	AC 600 V		APPLICABLE CABLE	600V VCT VINYL CABLE	
	CURRENT	20 A		APPLICABLE WIRE SIZE	INSURATOR OUTER DIA. ϕ 3.4mm CONDUCTOR CROSS SECTION 2.0mm ²	
SPECIFICATIONS						
ITEM		TEST METHOD		REQUIREMENTS	QT AT	
CONSTRUCTION						
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	X X	
MARKING		CONFIRMED VISUALLY.			X X	
ELECTRIC CHARACTERISTICS						
CONTACT RESISTANCE		CONTACT SHALL BE MEASURED AT DC 1 A.		5 mΩ MAX.	X —	
INSULATION RESISTANCE		500 V DC.		5000 MΩ MIN.	X —	
VOLTAGE PROOF		2100 V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.	X —	
MECHANICAL CHARACTERISTICS						
CONTACT INSERTION AND WITHDRAWAL FORCES		ϕ 2.362 ^{+0.003} ₀ BY STEEL GAUGE.		INSERTION AND WITHDRAWAL FORCES : 0.9N MIN.	X —	
CONNECTOR INSERTION AND WITHDRAWAL FORCES		MEASURED BY APPLICABLE CONNECTOR. LOCKING DEVICE WITH UNLOCK.		INSERTION AND WITHDRAWAL FORCES : 80 N MAX.	X —	
MECHANICAL OPERATION		100 TIMES INSERTIONS AND EXTRACTIONS.		CONTACT RESISTANCE: 10 mΩ MAX.	X —	
VIBRATION (RANDOM)		FREQUENCY 10 TO 100 Hz, DURABILITY TEST ASD LEVEL 11.83(m/S ²) ² /Hz, AT 5 h, FOR 3 DIRECTIONS. EARLY ANGULARITY 9dB/oct (5 TO 10 Hz), FINAL ANGULARITY -6dB/oct (100 TO 250 Hz). (REFER TO IEC 61373.)		①NO ELECTRICAL DISCONTINUITY OF 1 μs. ②NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X —	
SHOCK		490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 6 DIRECTIONS.		①NO ELECTRICAL DISCONTINUITY OF 1 μs. ②NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X —	
CONTACT RETENTION FORCE		APPLYING A PULL FORCE THE WIRE AFTER THE APPLICABLE CRIMPED CONTACT IS ASSEMBLED THE BODY.		30N MIN.	X —	
LOCK ACTIVITY		MEASURE THE TORQUE AT LOCK OR UNLOCK UNDER MATED APPLICABLE CONNECTOR.		1.2N · m MAX.	X —	
ENVIRONMENTAL CHARACTERISTICS						
DAMP HEAT (STEADY STATE)		EXPOSED AT 40 °C, 90 TO 95 %, 96 h.		① INSULATION RESISTANCE: 50 MΩ MIN (AT HIGH HUMIDITY), 500 MΩ MIN (AT DRY). ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X —	
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -40 → R/T ⁽¹⁾ → +105 → R/T °C TIME 30 → 2 TO 3 → 30 → 2 TO 3 min UNDER 200 CYCLES.		① INSULATION RESISTANCE: 5000 MΩ MIN. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X —	
CORROSION SALT MIST		EXPOSED IN 5 % SALT WATER SPRAY FOR 500 h.		NO DEFECT FOR LOCK ACTIVITY.	X —	
DRY HEAT		EXPOSED AT + 100 °C , 400 h.		NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X —	
COLD		EXPOSED AT - 40 °C , 400 h.		NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X —	
SEALING ⁽²⁾		EXPOSED AT A DEPTH OF 1 m FOR 0.5 h.		NO WATER PENETRATION INSIDE CONNECTOR.	X —	
AIRTIGHTNESS ⁽²⁾		APPLY AIR PRESSURE 19.6 kPa FOR 0.5 min TO INSIDE CONNECTOR.		NO AIR BUBBLES FROM INSIDE CONNECTOR.	X —	
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE	
①						
REMARK ABOVE SPECIFICATION SHOWS THE VALUES IN ASSEMBLED CONDITION WITH APPLICABLE CRIMP CONTACTS. NOTES (1) R/T : ROOM TEMPERATURE. (2) SEALING AND AIRTIGHTNESS. SHALL BE TESTED UNDER MATED CONDITION WITH AN APPLICABLE CONNECTOR. Unless otherwise specified, refer to IEC 60512.				APPROVED	HY. KOBAYASHI	16.04.01
				CHECKED	HY. KOBAYASHI	16.04.01
				DESIGNED	TH. KAMEYA	16.03.31
				DRAWN	TH. KAMEYA	16.03.31
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC-117729-00-00	
HRS	SPECIFICATION SHEET		PART NO.	HR43-21WBP-3SC		
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL143-0001-0-00		△ 1/1