




May.1.2022 Copyright 2022 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD					
Rating	Operating Temperature Range ⁽²⁾	-40°C to +105°C	Storage Temperature Range	-10°C to +60°C	
	Voltage	—	Applicable Cable ⁽¹⁾	①AWG#14 to 16 ② Wire Jacket Diameter ϕ 2.6 to 3.0	
	Current	20 A			
SPECIFICATIONS					
ITEM	TEST METHOD		REQUIREMENTS	QT	AT
CONSTRUCTION					
General Examination	Examined visually and with a measuring instrument.		According to the drawing.	X	X
ELECTRICAL CHARACTERISTICS					
Contact Resistance	Measured at DC 1A.		10 m Ω MAX.	X	X
MECHANICAL CHARACTERISTICS					
Contact Insertion and Extraction Forces	Measured with a ϕ 1.98 ^{+0.003} ₀ steel gauge.		Insertion and extraction forces: 1 N MIN.	X	—
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
					
REMARK			APPROVED	YH. YAMADA	20200128
Notes			CHECKED	HN. TANAKA	20200128
(1)The applicable cable should satisfy both conditions ① and ②.			DESIGNED	SH. KOYAMA	20200128
(2)Includes temperature rise due to current carrying.			DRAWN	SH. KOYAMA	20200128
Unless otherwise specified, refer to IEC 60512 (JIS C 5402).					
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.	ELC-390464-00-00	
	SPECIFICATION SHEET		PART NO.	BH12-SC-213	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL140-0014-0-00	 1/1