








注1 はんだ付け作業は40W以下のはんだこてを使用し、作業時間は4秒以下で行ってください。

△3 2 製品番号, HRS No. は下記となります。

芯数	製品番号	HRS No.
9	HDEB-9P(05)	CL0211-0232-6-05
15	HDAB-15P(05)	CL0211-0234-1-05
25	HDBB-25P(05)	CL0211-0215-7-05
37	HDCB-37P(05)	CL0211-0236-7-05
50	HDDB-50P(05)	CL0211-0393-5-05

	A	B	C	D	E	F	G	H	I	J	K	L
9	30.81	24.99	16.9	8.34	12.55	5.99	1.2±0.3	19.28	10.72	24.99	20.2	11.5
15	39.14	33.32	25.24					27.55		33.32	28.6	
25	53.04	47.04	39.01	8.4		5.87	1.4±0.3	41.28		47.04	42.3	
37	69.32	63.5	55.47				1.5±0.5	57.71		63.5	58.7	
50	66.93	61.11	52.85	11.13	15.37		1.5±0.3	55.32	13.56	61.11	56	14.3

※50芯は端子配列が3段になります。

3	PBT樹脂	(クロ)UL94V-0						
2	PBT樹脂	(クロ)UL94V-0		5	鋼	表面部：ニッケルめっき 2μm min		
1	りん青銅	接触部：金めっき 0.2μm min	4			鋼	下地部：銅めっき 5μm min	
		下地部：ニッケルめっき 2μm min		表面部：ニッケルめっき 2μm min				
		結線部：金めっき 0.03μm min				下地部：銅めっき 5μm min		
No.	MATERIAL	FINISH , REMARKS		No.	MATERIAL	FINISH , REMARKS		
UNITS mm		SCALE 2 : 1	COUNT  1	DESCRIPTION OF REVISIONS DIS-E-00002118		DESIGNED TS. ITO	CHECKED MN. KENJO	DATE 20190219
 HIROSE ELECTRIC CO., LTD.		APPROVED :HO.MIWA	20061107	DRAWING NO. ADC-126117-00-00				
		CHECKED :YH.ENAMI	20061106	PART NO. HD*B-**P(05)				
		DESIGNED :MT.ITANO	20061106	CODE NO. CL211				
		DRAWN :MT.ITANO	20061106	 1				