


COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△				..	△				..
△				..	△				..
APPLICABLE STANDARD									
RATING	OPERATING TEMPERATURE RANGE	-10 ℃ TO 60 ℃			STORAGE TEMPERATURE RANGE	℃ TO ℃			
	VOLTAGE	V			CURRENT	A <input checked="" type="checkbox"/>			
	APPLICABLE CABLE								
SPECIFICATIONS									
ITEM	TEST METHOD				REQUIREMENTS			QT	AT
CONSTRUCTION									
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.				ACCORDING TO DRAWING.			<input type="checkbox"/>	<input type="checkbox"/>
MARKING	CONFIRMED VISUALLY.							<input type="checkbox"/>	<input type="checkbox"/>
ELECTRICAL CHARACTERISTICS									
CONTACT RESISTANCE	1 A (DC OR 1000 Hz). MEASUREMENT POINT SHALL BE AS FOLLOWS.				10 mΩ MAX.				
								<input type="checkbox"/>	<input type="checkbox"/>
(ONE EXAMPLE OF CONNECTOR CONFIGURATION IS SHOWN.)									
MECHANICAL CHARACTERISTICS									
MECHANICAL OPERATION	1000 TIMES INSERTIONS AND EXTRACTATIONS				① CONTACT RESISTANCE: 20 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.			<input type="checkbox"/>	-
ENVIRONMENTAL CHARACTERISTICS									
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -50 → 5 TO 35 → 85 → 5 TO 35 ℃ TIME 30 → 5 MAX. → 30 → 5 MAX. min UNDER 5 CYCLES.				① NO DAMAGE, CRACK AND LOOSENESS OF PARTS.			<input type="checkbox"/>	-
CORROSION SALT MIST	EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.				① CONTACT RESISTANCE: 20 mΩ MAX. ② NO HEAVY CORROSION.			<input type="checkbox"/>	-
REMARKS <input checked="" type="checkbox"/> AS PER FORROWING TABLE-1.									
Unless otherwise specified, refer to JIS C 5402.				DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED	
				J. Watanabe	J. Watanabe	H. Miura	S. Watanabe		
				'95.8.3	'95.8.3	95.8.3	95.8.4		
Note QT: Qualification Test AT: Assurance Test ○: Applicable Test									
HRS HIROSE ELECTRIC CO., LTD.				SPECIFICATION SHEET			PART NO. QR/P-XC-121 (12)		
CODE NO. (OLD) CL		DRAWING NO. ELC4-08218 -03			CODE NO. CL221-0010 -1-12			1/1	