

TO
Q1

	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE		COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△						△					
△						△					
APPLICABLE STANDARD											
RATING	OPERATING TEMPERATURE RANGE		— °C TO — °C			STORAGE TEMPERATURE RANGE		— °C TO — °C			
	VOLTAGE		—			OPERATING HUMIDITY RANGE		— % TO — %			
	CURRENT		—			APPLICABLE CABLE		—			
SPECIFICATIONS											
ITEM		TEST METHOD				REQUIREMENTS				QT	AT
CONSTRUCTION											
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.				ACCORDING TO DRAWING.				○	○
MARKING		CONFIRMED VISUALLY.								○	○
MECHANICAL CHARACTERISTICS											
VIBRATION		FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, — m/s <sup>2</sup> AT 2 h, FOR 3 DIRECTIONS.				NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.				○	—
SHOCK		490 m/s <sup>2</sup> DIRECTIONS OF PULSE 11 ms AT 3 TIMES FOR 6 DIRECTIONS.								○	—
LOCKING FORCE		PULL THE CONNECTOR, CABLE AXIALY. 294N, 1min								○	—
ENVIRONMENTAL CHARACTERISTICS											
CORROSION SALT MIST		EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.				NO HEAVY CORROSION.				○	—
REMARKS											
						DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED	
						T. Ito	T. Ito	Y. Enomi	2. (Muro)		
						'05.7.4	'05.7.4	05.09.04	'05.07.04		
Unless otherwise specified, refer to JIS C 5402.											
Note QT:Qualification Test AT:Assurance Test O:Applicable Test											
HRS HIROSE ELECTRIC CO., LTD.						SPECIFICATION SHEET			PART NO.		
									P-1624A-STA(51)		
CODE NO.(OLD)			DRAWING NO.			CODE NO.			1/1		
CL			ELC4-006260-01			CL216-0157-4-51					