







| APPLICABLE STANDARD | | | | | |
|--|---------------------------------------|---|---------------------------|------------------|---|
| RATING | OPERATING TEMPERATURE RANGE |  -25 °C TO 60 °C | STORAGE TEMPERATURE RANGE | -25 °C TO 60 °C | |
| | VOLTAGE | — | OPERATING HUMIDITY RANGE | 95 % MAX | |
| | CURRENT | — | APPLICABLE CABLE | — | |
| SPECIFICATIONS | | | | | |
| ITEM | TEST METHOD | | REQUIREMENTS | QT | AT |
| CONSTRUCTION | | | | | |
| GENERAL EXAMINATION | VISUALLY AND BY MEASURING INSTRUMENT. | | ACCORDING TO DRAWING. | X | X |
| MARKING | CONFIRMED VISUALLY. | | | X | X |
| | | | | | |
|  ① THE OPERATION TEMPERATURE INCLUDES THE TEMPERATURE RISE BY CURRENT CARRYING. ② TEMPERATURE RANGE FOR A CONNECTOR UNMATED. | | | | | |
| | COUNT | DESCRIPTION OF REVISIONS | DESIGNED | CHECKED | DATE |
|  | 1 | DIS-E-00002716 | TS. ITO | TU. TANIGUCHI | 20191127 |
| REMARK | | | APPROVED | RI. TAKAYASU | 20100617 |
| | | | CHECKED | YH. ENAMI | 20100617 |
| | | | DESIGNED | MT. ITANO | 20100617 |
| Unless otherwise specified, refer to IEC 60512.  | | | DRAWN | MT. ITANO | 20100617 |
| Note QT:Qualification Test AT:Assurance Test X:Applicable Test | | | DRAWING NO. | ELC-025515-61-01 | |
|  | SPECIFICATION SHEET | | PART NO. | TM11P-88P (61) | |
| | HIROSE ELECTRIC CO., LTD. | | CODE NO. | CL222-1328-2-61 |  1/1 |