

Apr.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	① -55 °C TO 85 °C	STORAGE TEMPERATURE RANGE	② -55 °C TO 85 °C	
	VOLTAGE	—	OPERATING HUMIDITY RANGE	95 % MAX	
	CURRENT	—	APPLICABLE CABLE	—	
SPECIFICATIONS					
ITEM	TEST METHOD	REQUIREMENTS	QT	AT	
CONSTRUCTION					
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X	
MARKING	CONFIRMED VISUALLY.		X	X	
ENVIRONMENTAL CHARACTERISTICS					
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55 → 5 ~ 35 → 85 → 5 ~ 35 °C TIME 30 → 2 ~ 3 → 30 → 2 ~ 3 min UNDER 5 CYCLES.	NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	X	—	
<p>① THE PRODUCT PERFORMANCE IS GUARANTEED ONLY IN THE TEMPERATURE ADEQUATE TO PEOPLE'S ACTIVITIES.</p> <p>② PACKING MATERIAL IS NOT INCLUDED.</p>					
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△					
REMARK			APPROVED	HO.MIWA	07.11.02
			CHECKED	YH.ENAMI	07.11.02
			DESIGNED	MT.ITANO	07.11.02
Unless otherwise specified, refer to JIS C 5402.			DRAWN	MT.ITANO	07.11.02
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.	ELC4-007305-01	
HRS	SPECIFICATION SHEET		PART NO.	1600-LC	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL216-0354-5-00	△ 1/1