

Apr.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	1 -55 °C TO 85 °C	STORAGE TEMPERATURE RANGE	2 -55 °C TO 85 °C	
	VOLTAGE	—	OPERATING HUMIDITY RANGE	95 % MAX	
	CURRENT	—	APPLICABLE CABLE	—	
SPECIFICATIONS					
ITEM		TEST METHOD		REQUIREMENTS	QT AT
CONSTRUCTION					
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	X X
MARKING		CONFIRMED VISUALLY.			X X
ENVIRONMENTAL CHARACTERISTICS					
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55 → 5 ~ 35 → 85 → 5 ~ 35 °C TIME 30 → 2 ~ 3 → 30 → 2 ~ 3 min UNDER 5 CYCLES.		NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	X —
1 THE PRODUCT PERFORMANCE IS GUARANTEED ONLY IN THE TEMPERATURE ADEQUATE TO PEOPLE'S ACTIVITIES. 2 PACKING MATERIAL IS NOT INCLUDED.					
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
Δ					
REMARK  Unless otherwise specified, refer to JIS C 5402.			APPROVED	HO.MIWA	07.11.02
			CHECKED	YH.ENAMI	07.11.02
			DESIGNED	MT.ITANO	07.11.02
			DRAWN	MT.ITANO	07.11.02
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC4-007305-01
HRS	SPECIFICATION SHEET		PART NO.	1600-LC	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL216-0354-5-00	Δ 1/1