


APPLICABLE STANDARD				
RATING	OPERATING TEMPERATURE RANGE	$\triangle 1$ -55 °C TO +85 °C $\triangle 1$	STORAGE TEMPERATURE RANGE	-25 °C TO +60 °C
	VOLTAGE	125 V AC	OPERATING HUMIDITY RANGE	95 % MAX
	CURRENT	500 mA	APPLICABLE CABLE	—
SPECIFICATIONS				
ITEM	TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION				
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X
MARKING	CONFIRMED VISUALLY.		X	X
ELECTRIC CHARACTERISTICS				
CONTACT RESISTANCE	100 mA (DC OR 1000 Hz AC).  (AN EXAMPLE OF CONNECTOR CONFIGURATION IS SHOWN.)	200 mΩ MAX.	X	X
INSULATION RESISTANCE	100 V DC.	100 MΩ MIN.	X	X
VOLTAGE PROOF	500 V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	X	X
MECHANICAL CHARACTERISTICS				
MECHANICAL OPERATION	200 TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE : 220 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X	—
VIBRATION	FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, AT 10 CYCLES.	① NO ELECTRICAL DISCONTINUITY OF 5 μs. ② CONTACT RESISTANCE : 220 mΩ MAX.	X	—
SHOCK	490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.	③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X	—
ENVIRONMENTAL CHARACTERISTICS				
DAMP HEAT, CYCLIC	EXPOSED AT +40 °C, 90 TO 95 %, 500 h	① CONTACT RESISTANCE : 220 mΩ MAX. ② INSULATION RESISTANCE : 1 MΩ MIN. (AT HIGH HUMIDITY) 10 MΩ MIN. (AT DRY) ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X	—
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55±3 → 5 TO 35 → 85±2 → 5 TO 35 °C TIME 30 TO 35 → 5 MAX → 30 TO 35 → 5 MAX MIN. UNDER 5 CYCLES.	① INSULATION RESISTANCE : 100 MΩ MIN. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X	—
CORROSION SALT MIST	EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.	① CONTACT RESISTANCE : 220 mΩ MAX. ② NO HEAVY CORROSION.	X	—
RESISTANCE TO SOLDERING HEAT	SOLDER TEMPERATURE, 260 ± 5 °C FOR IMMERSION, DURATION 10 ± 1 S.	NO DEFORMATION OF CASE AND EXCESSIVE LOOSENESS OF THE TERMINALS.	X	—
SOLDERABILITY	SOLDERED AT SOLDER TEMPERATURE, 245 ± 2 °C FOR IMMERSION, DURATION 3 ± 1 S.	MIN. 95 % OF SOLDER IMMERSED AREA SHALL BE COVERED NEW SOLDER COATING.	X	—
COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
$\triangle 1$ 2	DIS-E-00002716	TS. ITO	TU. TANIGUCHI	20191127
REMARK $\triangle 1$ ① THE PRODUCT PERFORMANCE IS GUARANTEED ONLY IN THE TEMPERATURE ADEQUATE TO PEOPLE'S ACTIVITIES. ② THE OPERATION TEMPERATURE INCLUDES THE RISE BY CURRENT CARRYING. Unless otherwise specified, refer to IEC 60512. $\triangle 1$		APPROVED	YH. ENAMI	20100224
		CHECKED	HO. MIWA	20100224
		DESIGNED	HN. ANDO	20100223
		DRAWN	HN. ANDO	20100223
Note QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.	ELC-023897-50-02	
HRS	SPECIFICATION SHEET	PART NO.	TM5RJ1-64 (50)	
	HIROSE ELECTRIC CO., LTD.	CODE NO.	CL222-1244-4-50	$\triangle 1$ 1/1