


COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△	3	RE-E-08257	K.H	A-5	△				
△				61.12.2/	△				

APPLICABLE STANDARD		TIA/EIA-568-B.2 CATEGORY5e △							
RATING	OPERATING TEMPERATURE RANGE	-25 °C TO 60 °C				STORAGE TEMPERATURE RANGE	-25 °C TO 60 °C		
	VOLTAGE	125 V AC				CURRENT	1 A △		

SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT		
CONSTRUCTION						
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	○	○		
MARKING	CONFIRMED VISUALLY.		○	○		
ELECTRIC CHARACTERISTICS						
CONTACT RESISTANCE	100 mA (DC OR 1000 Hz AC). MEASUREMENT POINTS SHALL BE AS FOLLOWS  (ONE EXAMPLE OF CONNECTOR CONFIGURATION IS SHOWN.)	230 mΩ MAX.	○	○		
INSULATION RESISTANCE	100 V DC.	100 MΩ MIN.	○	○		
VOLTAGE PROOF	500 V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	○	○		
NEAR END CROSSTALK(NEXT)LOSS	MEASURED MINIMUM NEXT LOSS FOR EACH PAIR COMBINATION AT 100 Hz	43 dB MIN. △	○	—		
MECHANICAL CHARACTERISTICS						
MECHANICAL OPERATION	200 TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE: 250 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	○	—		
VIBRATION	FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, — m/s² AT 2 h, FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 5 μs. ② CONTACT RESISTANCE: 250 mΩ MAX.	○	—		
SHOCK	490 m/s² DIRECTIONS OF PULSE 11 ms AT 3 TIME FOR 3 DIRECTION.	③ NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	○	—		
ENVIRONMENTAL CHARACTERISTICS						
DAMP HEAT (STEADY STATE)	EXPOSED AT 40 °C, 90 TO 95 %, 500 h.	① CONTACT RESISTANCE: 250 mΩ MAX. ② INSULATION RESISTANCE: 1 MΩ MIN. (AT HIGH HUMIDITY) ③ INSULATION RESISTANCE: 10 MΩ MIN. (AT DRY) ④ NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	○	—		
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55±3 →5 TO 35→85±2 →5 TO 35°C TIME 30 TO 35→5 MAX→30 TO 35 →5 MAX min UNDER 5 CYCLES.	① CONTACT RESISTANCE: 250 mΩ MAX. ② INSULATION RESISTANCE: 100 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	○	—		
CORROSION SALT MIST	EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.	① CONTACT RESISTANCE: 250 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	○	—		
REMARKS		DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
		S.Sato 00.07.03	S.Sato 00.07.03	T.Watanabe 00.07.03	H.Miwa 00.07.03	
Unless otherwise specified, refer to JIS C 5402.						
Note QT:Qualification Test AT:Assurance Test ○:Applicable Test						
HS HIROSE ELECTRIC CO., LTD.		SPECIFICATION SHEET		PART NO. TM21P - 88P 「 」		
CODE NO.(OLD)	DRAWING NO. ELC4 - 121484 - 04	CODE NO.	CL 222 - 2862 - 9 - 「 」			

TO
Q2