APPLICABLE STANDARD		UL, C-UL TUV STANDARD	(Appendix	1)						
	Operating		-40 °C TO +105 °C (Note	1)	Storage 1	Γemperatur	е			
	Temperatur	re Range	(Included temperature ris	е	Range		-4	0 °C TO +60 °C (No	te 2)	
			caused by current-carryin	g)						
RATING	Voltage		(Appendix 1)		Current			A (UL, C-UL, TUV) (A A (Derating curve:		1)
			14sq to 50sq					(Appendix 2)	,	
	Applicable	e Wire	(AWG#5 to AWG#1/0)				ne Rating Current for each can be found in table 3.	applicab	le wire
			SPEC	IFICATI	ONS		0120	our so round in custo c.		
	TEM		TEST METHOD				REQUIT	REMENTS	QT	AT
CONSTRU			TEOT METHOD				TLEGO1	KEMENTO	Q1	Λ1
General Exami		Visually	and by measuring instrument.		Accord	ing to draw	ing.		х	Х
Marking		Confirmed	l visually.						X	Х
ELECTRIC	AL CHARA	ACTEREIS	TICS							
Contact Resis	tance	DC 1 A			0.3 mΩ	MAX.			Х	Х
Insulation Re	sistance	250 V DC			5000 M	Ω MIN.			Х	
Voltage Proof	:	2000 V AC	c. for 1 min.		No flas	shover or bi	reakdo	wn.	X	<u> </u>
MECHANIC	CAL CHAR	<u> </u>	TICS							
Mating and Ur	mating Force		by applicable connector at a sp	peed of	Matinge	e force : 49	9 N MA	Х.	Х	_
		30 mm ± 3	3 mm/min.		Unmatir	ng force : 4	49 N M	AX.	X	_
Mechanical Op	eration	100 times	insertions and extractions at speed of 600		00 Cont	ant register	200 oh	ang : 0.5 mO MAY	v	
		times/hou			UO ①Contact resistance chang : 0.5 mΩ MAX. ②No damage, crack and looseness of parts.		X			
Vibration		Frequency	: 10 to 55 hz, singe amplitude	e 0.75 mm,	① No e	① No electrical discontinuity of 10 μ s.			Х	_
		at 5 min/	cycle, 10 cycles each in 3 ax	is directio	ns. ② No d	damage. crad	ck and	looseness of parts.		
Shock			s in total. duration of pulse 11 ms at 3 ti	maa						
SHOCK			ch axial directions.	illes			Х	_		
ENVIRON	/ENTAL C	<u> </u>	RISTICS							
			ure -40 → 105 °C		①Conta	act resista	nce ch	nange: $0.5 \text{ m}\Omega$ MAX.	Х	Ι_
Rapid Change		Time	$30 \rightarrow 30 \text{ min}$		0	②Insulation resistance : 1000 M Ω MIN.				
of Temperatur	е		transfer time is 2 to 3 min. 5 cycles of above cycles(mated)		③No da	③No damage.crack and looseness of parts.				
			sed in the room temperature for	1 to 2 hou	rs.					
Humidity Life			After exposure at temperature 40 ± 2 °C, humidity 90 to		-			Х	_	
			%, for 96 h. (mated), exposed at room temperatrure r 1 to 2 hour.			21113d1dt10111C313td110C : 1000 m22 m114.				
		101 1 10	Z Hour.		3)No di	amage.crack	and I	ooseness of parts.		
Heat Resistar	ice	After exp	posure at temperature 105±2 °c,		①Cont	act resista	nce ch	nange: $0.5 \text{ m}\Omega$ MAX.	Х	_
			for 96 h(mated), exposed at ro	om temperat	<u>_</u> 1110u	$ \begin{tabular}{lllllllllllllllllllllllllllllllllll$				
Cold Resistar	100	for 1 to	z nour. posure at -40±3 °C, 96 h.(mated)					-	
COTO NESTSEAL	106		at room temperatrur for 1 to 2		-				Х	_
					_					
Corrosion Sal	t Mist		oosure in 35±2°c, 5±1% salt w nated),washed with water,dried		for No hea	or No heavy corrosion that lose function.		: lose function.	Х	_
			ure and humidity for 24 hours.	at norman						
COUN	Т	DESCRIPTI	ON OF REVISIONS	DI	ESIGNED			CHECKED	DA	TE
<u>↑</u> 1		DIS-	-E-00000869	TA	. TORIHARA	Libbooks	_	AH. KODAMA)4. 14
REMARK (Note 1) Th	e operation	temperature i	ncludes the temperature rise b	y current c	arrying.	APPROVE	ע	NM. NISHIMATSU	_	7. 23
(Note 2) Storage temperature range shows					CHECKED		NM. NISHIMATSU	-	7. 23	
af	er mounting.		e operating temperature range 1	or storage	CONCILION	DESIGNE	ν	WR. YAMADA		7. 22
			er to IEC 60512.	I		DRAWN		WR. YAMADA)7. 22
Note Q1:Qu	1		rance Test X:Applicable Test	1	ING NO.		E	ELC4-128553-00		
HS			CATION SHEET		T NO.	-	000	PS3C-B-1US		
	HIR	OSE ELE	ECTRIC CO., LTD.	COL	DE NO	CL2	236-	-1063-2-00	/ 1\	1/7

Appendix 1. Condition of safety standard (UL, C-UL, TUV STANDARD)

This item got approved by safety standard(UL, C-UL, TUV STANDARD) under the condition of table 1 and table 2. Safety standard is different up to the applied rated voltage and current please see the table 1 and table 2.

Table 1. UL, C-UL condition

	Condition 1	Condition 2	
Current voltage(ac/dc)		600V	
Current rating	100A	150A	
Cable	14 to 22sq AWG#5 to AWG#3 (*1)	38 to 50sq AWG#1 to AWG#1/0 (*1)	
Creepage distance(*2)	MIN:3.2mm		
Clearance distance(*2)	MIN:3.2mm		

Table 2. TUV conditon

	Condition I	Condition I	Condition Ⅲ		
Current voltage(ac/dc)	800∨	600V	1000V		
	100A(cable 14 to	22sq , AWG#5 to	AWG#3 *1)		
Current rating	125A(cable 38sq	, AWG#1 *1)			
	150A(cable 50sq , AWG#1/0 *1)				
Over voltage category	п				
Pollution degree	3				
Creepage distance(*2)	MIN:12.6mm	MIN:12.6mm	MIN:16mm		
Clearance distance(*2)	MIN:6mm	MIN:6mm	MIN:8mm		
Insulation system	Basic insulation(panel has the earth)				

*1: As screws and crimp terminal attached with power contact have an impact on the creepage distance and the clearance distance, please use recommended screws and crimp terminals. In case you use cables other than following recommended screws and contacts, please be careful that the creepage distance and the clearance distance meet the standard of UL, C-UL, TUV.

-Recommended screw : JIS B 1188 spring washer + cross recessed pan head screw with captive

polished circular washer M6 X 12

-Recommended crimp terminal

Cable 14sq : JIS C 2805 R14-6 Cable 22sq : JIS C 2805 R22-6


Cable 38sq : Manufactured by NICHIFU CO.,LTD R38-6S Cable 50sq : Manufactured by NICHIFU CO.,LTD R60-6S


- *2: The coverage of the creepage distance and the clearance distance is as follows.
 - -Between plus power supply contact and minus power supply contact
 - -Between plus crimp terminal and minus crimp terminal
 - -Between power contact and panel
 - -Between crimp terminal and panel
 - -Between screws (attacehd with power contact) and panel

Note QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO	ELC4-128553-00)	
K 5	SPECIFICATION SHEET	PART NO	PS3C-B-1US		
Т	HIROSE ELECTRIC CO., LTD.	CODE NO	CL236-1063-2-00	\triangle	2/7

Appendix 2. Derating curve (reference)

i. 14 sq cable







- Note 1: Derating curve takes manufacturing tolerances into consideration as well as uncertainties in temperature measurement and the measuring set up and is derived from the base curve multiplied by 0.8 calculation.
 - 2: The value of rated current differs depending on the ambient temperature.
 - It is recommended to use the product within the derating curve zone.
 - If used under UL or TUV STANDARD, please refer to the appendix 1.
 - 3: Measurement method of derating curve is shown below.
 - -Test specimen: PS3-2US(female contact side connector, using the same contacts as the here handled PS3C-A-1US)
 - PS3-2UP(male contact side connector)
 - -Test cable spec: 14 mm² (AWG#5)
 - -Test condition: Turn on electricity under the static state and measure.

Note QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO	ELC4-128553-00		
HS.	SPECIFICATION SHEET	PART NO	PS3C-B-1US		
Т	HIROSE ELECTRIC CO., LTD.	CODE NO	CL236-1063-2-00	$\hat{\Lambda}$	3/7

Appendix 2. Derating curve (reference)

ii. 22 sq cable







- Note 1: Derating curve takes manufacturing tolerances into consideration as well as uncertainties in temperature measurement and the measuring set up and is derived from the base curve multiplied by 0.8 calculation.
 - 2: The value of rated current differs depending on the ambient temperature. It is recommended to use the product within the derating curve zone. If used under UL or TUV STANDARD, please refer to the appendix 1.
 - 3: Measurement method of derating curve is shown below.
 - -Test specimen: PS3-2US(female contact side connector, using the same contacts as the here handled PS3C-A-1US)
 PS3-2UP(male contact side connector)
 - -Test cable spec : 22 mm² (AWG#3)
 - -Test condition: Turn on electricity under the static state and measure.

Note QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO	ELC4-128553-00	
HS.	SPECIFICATION SHEET	PART NO	PS3C-B-1US	
1.0	HIROSE ELECTRIC CO., LTD.	CODE NO	CL236-1063-2-00 🗘 4/	′7

Appendix 2. Derating curve (reference)

iii. 38 sq cable





- Note 1: Derating curve takes manufacturing tolerances into consideration as well as uncertainties in temperature measurement and the measuring set up and is derived from the base curve multiplied by 0.8 calculation.
 - 2: The value of rated current differs depending on the ambient temperature. It is recommended to use the product within the derating curve zone. If used under UL or TUV STANDARD, please refer to the appendix 1.
 - 3: Measurement method of derating curve is shown below.
 - -Test specimen: PS3-2US(female contact side connector, using the same contacts as the here handled PS3C-A-1US)
 PS3-2UP(male contact side connector)


-Test cable spec : 38 mm² (AWG#1)


-Test condition: Turn on electricity under the static state and measure.

Note QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO	ELC4-128553-00)	
HS.	SPECIFICATION SHEET	PART NO	PS3C-B-1US		
Т	HIROSE ELECTRIC CO., LTD.	CODE NO	CL236-1063-2-00	\triangle	5/7

Appendix 2. Derating curve (reference)

iv. 50 sq cable





- Note 1: Derating curve takes manufacturing tolerances into consideration as well as uncertainties in temperature measurement and the measuring set up and is derived from the base curve multiplied by 0.8 calculation.
 - 2: The value of rated current differs depending on the ambient temperature. It is recommended to use the product within the derating curve zone. If used under UL or TUV STANDARD, please refer to the appendix 1.
 - 3: Measurement method of derating curve is shown below.
 - -Test specimen: PS3-2US (female contact side connector, using the same contacts as the here handled PS3C-A-1US)

PS3-2UP (male contact side connector)

- -Test cable spec $: 50 \text{ mm}^2 \text{ (AWG} \# 1/0)$
- -Test condition: Turn on electricity under the static state and measure.

Note QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO	ELC4-128553-00)	
HS.	SPECIFICATION SHEET	PART NO	PS3C-B-1US		
Т	HIROSE ELECTRIC CO., LTD.	CODE NO	CL236-1063-2-00	\triangle	6/7

Table 3. List of the rated current for each applicable wire size.

STANDARD Applicable wire	UL/C-UL (Appendix 1)	TUV (Appendix 1)	Derataing curve Ambient temperature 25°C (Appendix 2)
14mm ² , AWG#5	100A	100A	100A
22mm ² , AWG#3	100A	100A	125A
38mm ² , AWG#1	150A	125A	190A
50mm ² , AWG#1/0	150A	150A	210A

Note QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO	ELC4-128553-00)	
HS.	SPECIFICATION SHEET	PART NO	PS3C-B-1US		
I VO	HIROSE ELECTRIC CO., LTD.	CODE NO	CL236-1063-2-00	\triangle	7/7