

APPLICABLE STANDARD						
RATING	OPERATING TEMPERATURE RANGE	-40 °C TO +105 °C		STORAGE TEMPERATURE RANGE	-40 °C TO +60 °C	
	VOLTAGE	300 V AC,DC		CURRENT	5 A	
SPECIFICATIONS						
ITEM		TEST METHOD		REQUIREMENTS		QT AT
CONSTRUCTION						
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.		X X
MARKING		CONFIRMED VISUALLY.				X X
<div><div></div>THE OPERATION TEMPERATURE INCLUDES THE RISE BY CURRENT CARRYING.<div></div>STORAGE TEMPERATURE RANGE SHOWS STORAGE CONDITION FOR UNUSED PRODUCTS INCLUDING PACKING MATERIALS.FOLLOW THE OPERATING TEMPERATURE RANGE FOR STORAGE CONDITION AFTER MOUNTING.</div>						
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE	
REMARK				APPROVED	RI. TAKAYASU	15.06.25
				CHECKED	NM. NISHIMATSU	15.06.25
				DESIGNED	MO. SHIMOYAMA	15.06.23
				DRAWN	MO. SHIMOYAMA	15.06.23
Unless otherwise specified, refer to JIS C 5402.						
Note	QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.		ELC-128944-00-00	
	SPECIFICATION SHEET		PART NO.	PS2-1618PCFA-1000A		
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL236-1069-0-00		1/1