


In case	TO



5 PLATING
SURFACE AREA (PART) GOLD 0.03 μ m min.
UNDER PLATING NICKEL 1 μ m min.

FIGURE FOR PARAGING(FREE)

Technical drawing of a paraging-free component. The drawing includes a side view, a top view, and a detail view of the bottom edge.

Side View (Left): Shows the component's profile with dimensions 34 ± 0.15 and 2 ± 0.5 . The inner diameter is $(\phi 80)$ and the outer diameter is $(\phi 330)$.

Top View (Middle): Shows the circular top surface with a central hole of diameter $\phi 13 \pm 0.5$. An arrow indicates the "UNWINDING DIRECTION".

Detail View (Right): Shows the bottom edge of the component with dimensions 4 ± 0.15 , 2 ± 0.15 , 12 ± 0.15 , 1.75 ± 0.15 , 14.2 ± 0.15 , and 32 ± 0.3 . The detail view shows a series of rectangular features with rounded ends, labeled with callouts 4 and 5. The detail view also shows a circular feature with dimensions $(\phi 1.5)$ and $(\phi 0.75)$.

Bottom View (Bottom): Shows the bottom surface of the component with dimensions (4.9) and (0.2) . The bottom view also shows a circular feature with dimensions (1.7) and $(\phi 0.75)$.

Q2