

Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.




HRS DRAWING FOR REFERENCE

A−A



B−B



NOTES
1. APPLICABLE WIRE IS AWG #16～#18. (UL1007, UL1015) INSULATION DIAMETER φ3.30mm MAX.
2. APPLICABLE CRIMPING MACHINE AND CRIMPING CONDITIONS (CRIMP HEIGHT etc.) WILL BE SPECIFIED ACCORDING TO AWG # OR WIRE APPLIED.
3. ONE PACKAGE CONSISTS OF 100 PCS.
△2 4. REFER TO ATAI-E3038 FOR CRIMP QUALITY STANDARDS.

NO.	MATERIAL	FINISH , REMARKS
1	COPPER ALLOY	CONTACT AREA : GOLD PLATING 0.2μm MIN. TERMINAL AREA : TIN PLATING 1μm MIN. UNDER PLATING : NICKEL PLATING 0.5μm MIN.

NO.	MATERIAL	FINISH , REMARKS

UNITS	SCALE		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm	5 : 1	△2	1	DIS-E-004910	TY. MIURA	NM. NISHIMATSU	14. 01. 20

HIROSE ELECTRIC CO., LTD.

APPROVED	RI. TAKAYASU	12. 12. 11
CHECKED	AH. KODAMA	12. 12. 11
DESIGNED	TY. MIURA	12. 12. 10
DRAWN	TY. MIURA	12. 12. 10

DRAWING NO.	EDC3-128191-00
PART NO.	PQ50-1618SCA
CODE NO.	CL236-2044-3-00

△2 1/1

FORM HC0011-5-7