



May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

△ Shape change



- Note
- 1 Mating key type is 'I'.
 - 2 The screw which attaches plug case (ref No. ②, ③ assembly) and cover case (ref No. ①・④・⑤・⑥・⑦・⑧ assembly) is appended products.
(recommended tightening torque: 0.32~0.63 N・m)
 - 3 Use recommended screw (commercial item) to attach the crimp terminal to this product.
(recommended screw JIS B 1188 cross recessed pan head machine screw with captive washer M3×0.5×4
(recommended tightening torque: 0.32~0.63 N・m)
 - 4 Refer to ETAD-E3149 for the conformity connectors with this product.
 - 5 Refer to ETAD-E3151 for the procedure of the cable assembly.
 - 6 This is a die casting product. molten metal flow patterns and small roughness may appear on the surface.
However there is no problem in the product functions.
 - 7 Sales unit: 20 pcs/box.


4	Stainless steel		9	Steel	Nickel plating
3	Stainless steel	Nickel plating	8	Steel	Nickel plating
2	Aluminum alloy		7	Steel	Nickel plating
1	Aluminum alloy		6	Stainless steel	
			5	Stainless steel	
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 1 : 1	COUNT △ 5	DESCRIPTION OF REVISIONS DIS-E-00004819	
HRS HIROSE ELECTRIC CO., LTD.		APPROVED	RI. TAKAYASU	20160621	DRAWING NO. EDC-129063-00-00
		CHECKED	NM. NISHIMATSU	20160621	PART NO. PQ50WA-2U-PC1
		DESIGNED	TY. MIURA	20160621	CODE NO. CL0236-2089-0-00
		DRAWN	TY. MIURA	20160621	
		DESIGNED	HY. MATSUDA	20210326	DATE 20210326



May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

△ Shape change

Cover case
(Ref No. ①・④・⑤・⑥・⑦・⑧ assembly)



HRS	DRAWING NO.	EDC-129063-00-00	2/3
	PART NO.	PQ50WA-2U-PC1	
	CODE NO.	CL0236-2089-0-00	