

Applicable Standard					
Rating	Operating Temperature Range	-10℃ to +60℃	Storage Temperature Range	-10℃ to +60℃	
	Voltage	—	—	—	
	Current	—	Applicable Cable	—	
SPECIFICATIONS					
ITEM		TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION					
General Examination		Visually and by measuring instrument.	According to drawing.	X	X
Marking		Confirmed visually.		X	X
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
REMARK			APPROVED	RI. TAKAYASU	18.08.22
			CHECKED	AH. KODAMA	18.08.22
			DESIGNED	TY. MIURA	18.08.22
			DRAWN	TY. MIURA	18.08.22
Unless otherwise specified, refer to IEC 60512.					
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC-129786-00-00
	SPECIFICATION SHEET		PART NO.	PQ50WA-1U-FL-DC	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL236-2124-0-00	1/1