




Apr.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-25°C TO +85°C	STORAGE TEMPERATURE RANGE	-25°C TO +60°C	
	OPERATING&STORAGE HUMIDTY RANGE	85 % MAX	APPLICABLE CABLE	CABLE DIAMETER : $\phi 6.6\pm 0.5$	
SPECIFICATIONS					
ITEM		TEST METHOD		REQUIREMENTS	QT AT
CONSTRUCTION					
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	X X
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
					
REMARK  Unless otherwise specified, refer to JIS C 5402.			APPROVED	RI. TAKAYASU	11. 07. 14
			CHECKED	YH. ENAMI	11. 07. 14
			DESIGNED	YH. MAMADA	11. 07. 14
			DRAWN	YH. MAMADA	11. 07. 14
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC4-127607-00
	SPECIFICATION SHEET		PART NO.	DH-17-CMB (6. 6)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL244-0063-1-00	 1/1