




Feb. 1. 2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-25°C TO +85°C	STORAGE TEMPERATURE RANGE	-25°C TO +60°C	
	OPERATING&STORAGE HUMIDTY RANGE	85 % MAX	APPLICABLE CABLE	CABLE DIAMETER : $\phi 6.6 \pm 0.5$	
<b>SPECIFICATIONS</b>					
ITEM	TEST METHOD	REQUIREMENTS	QT	AT	
<b>CONSTRUCTION</b>					
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X	
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
					
REMARK  Unless otherwise specified, refer to JIS C 5402.			APPROVED	RI. TAKAYASU	11. 07. 14
			CHECKED	YH. ENAMI	11. 07. 14
			DESIGNED	YH. MAMADA	11. 07. 14
			DRAWN	YH. MAMADA	11. 07. 14
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.	ELC4-127607-00	
	SPECIFICATION SHEET		PART NO.	DH-17-CMB (6. 6)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL244-0063-1-00	 1/1