

APPLICABLE STANDARD					
RATING	Operating Temperature Range	-25°C to +85°C	Storage Temperature Range	1 -25°C to +60°C	
	Voltage	—	Current	—	
SPECIFICATIONS					
ITEM		TEST METHOD		REQUIREMENTS	QTAT
CONSTRUCTION					
General Examination		Examined visually and with a measuring instrument.		According to drawing.	XX
Marking		Confirmed visually.		According to drawing.	XX
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
1	0				
REMARK 1 The storage temperature range indicates the storage conditions in the unused state including the packaging material. The operating temperature range applies to the storage conditions after product mounting. Unless otherwise specified, refer to JIS C 5402.			APPROVED	MN.KENJO	20210512
			CHECKED	KG.OKITA	20210512
			DESIGNED	HY.MATSUDA	20210512
			DRAWN	HY.MATSUDA	20210512
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC-127428-00-00
HRS	SPECIFICATION SHEET		PART NO.	DH-17P-DC	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL0244-0061-6-00	1/1