

APPLICABLE STANDARD				
RATING	OPERATING TEMPERATURE RANGE -25°C TO +85°C			
	STORAGE TEMPERATURE RANGE -25°C TO +60°C			
	OPERATING&STORAGE HUMIDTY RANGE 85 % MAX			
	APPLICABLE CABLE			
	CABLE DIAMETER : ϕ5.6±0.5			
SPECIFICATIONS				
ITEM	TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION				
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X
<div></div>				
COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
<div></div>				
REMARK		APPROVED	RI. TAKAYASU	11. 09. 13
		CHECKED	YH. ENAMI	11. 09. 13
		DESIGNED	YH. MAMADA	11. 09. 09
Unless otherwise specified, refer to JIS C 5402.		DRAWN	YH. MAMADA	11. 09. 09
Note QT:Qualification Test AT:Assurance Test X:Applicable Test	DRAWING NO.		ELC4-127675-00	
HRS	SPECIFICATION SHEET	PART NO.	DH-17-CMB (5. 6)	
	HIROSE ELECTRIC CO., LTD.	CODE NO.	CL244-0064-4-00	<div></div> 1/1