

APPLICABLE STANDARD							
RATING	OPERATING TEMPERATURE RANGE	-55°C TO +125°C(95%RH MAX)		STORAGE TEMPERATURE RANGE	-55°C TO +125°C(95%RH MAX)		
	POWER	_____ W		CHARACTERISTIC IMPEDANCE	50 Ω (DC TO 40 GHz)		
	PECULIARITY	_____		APPLICABLE CABLE	_____		
SPECIFICATIONS							
ITEM	TEST METHOD			REQUIREMENTS	QT	AT	
CONSTRUCTION							
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.			ACCORDING TO DRAWING.	X	X	
MARKING	CONFIRMED VISUALLY.				X	X	
ELECTRIC CHARACTERISTICS							
CONTACT RESISTANCE	100 mA MAX (DC OR 1000 Hz).			CENTER CONTACT	12 mΩ MAX.	X	X
				OUTER CONTACT	12 mΩ MAX.	X	X
INSULATION RESISTANCE	250 V DC.			500 MΩ MIN.		X	X
VOLTAGE PROOF	500 V AC FOR 1 min.CURRENT LEAKAGE 2mA MAX.			NO FLASHOVER OR BREAKDOWN.		X	X
VSWR	FREQUENCY DC TO 40 GHz.			VSWR <1.15 : DC TO 10 GHz <1.25 : 10 TO 30 GHz <1.38 : 30 TO 40 GHz		X	X
INSERTION LOSS	FREQUENCY DC TO 40 GHz			0.5 dB MAX.		X	X
MECHANICAL CHARACTERISTICS							
CONTACT INSERTION AND EXTRACTION FORCES	BY STEEL GAUGE.			INSERTION FORCE	N MAX.	-	-
				EXTRACTION FORCE	NMIN	-	-
INSERTION AND WITHDRAWAL FORCES	MEASURED BY APPLICABLE CONNECTOR. [APPLICABLE CONNECTOR : SMPJ-HKJ]			INSERTION FORCE	65 N MAX.	X	-
				EXTRACTION FORCE	16 N MAX.	X	-
MECHANICAL OPERATION	100 TIMES INSERTIONS AND EXTRACTIONS. [SMP SIDE] 500 TIMES INSERTIONS AND EXTRACTIONS. [HK SIDE] [APPLICABLE CONNECTOR : SMPJ-HKJ]			1) CONTACT RESISTANCE: CENTER CONTACT 20 mΩMAX.CHANGE OUTER CONTACT 20 mΩMAX.CHANGE 2) NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		X	-
VIBRATION	FREQUENCY 10 TO 500 Hz SINGLE AMPLITUDE 0.75 mm, 98 m/s ² AT 10 CYCLES FOR 3 DIRECTIONS.			1)ELECTRICAL CHARACTERISTIC SHALL BE MET. 2) NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		X	-
SHOCK	490 m/s ² DIRECTIONS OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.					X	-
CABLE CLAMP ROBUSTNESS (AGAINST CABLE PULL)	APPLYING A PULL FORCE THE CABLE AXIALLY AT N MAX.			1) NO WITHDRAWAL AND BREAKAGE OF CABLE. 2) NO BREAKAGE OF CLAMP.		-	-
ENVIRONMENTAL CHARACTERISTICS							
DAMP HEAT,CYCLIC	EXPOSED AT -10 TO +65 °C, 90~98 % TOTAL 10 CYCLES (240 h)			1) INSULATION RESISTANCE: 100 MΩ MIN. (AT HIGH HUMIDITY) 2) INSULATION RESISTANCE: 500 MΩ MIN. (AT DRY) 3) NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		X	-
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55 → - → +125 → - °C TIME 30 → 3 → 30 → 3 min. UNDER 5 CYCLES.			NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		X	-
CORROSION SALT MIST	EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.			ELECTRICAL CHARACTERISTIC SHALL BE MET.		X	-
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE		
REMARK RoHS COMPLIANT The above VSWR and INSURTION LOSS performance is confirmed when SMPJ-HKJ is mated to SMPP(FD)-HKP. Unless otherwise specified, refer to IEC 60512.	△						
			APPROVED	TS. NOBE	17.09.12		
			CHECKED	TS. NOBE	17.09.12		
			DESIGNED	AH. MARUYAMA	17.09.12		
		DRAWN	AH. MARUYAMA	17.09.12			
Note	QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.	ELC-370824-00-00			
HRS	SPECIFICATION SHEET		PART NO.	SMPP (FD) -HKP			
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL311-0199-0-00	△	1/1	