






Jul.1.2022 Copyright 2022 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

| APPLICABLE STANDARD   |   | IEC 61076-3-124                        |   |   |          |
|---|---|--|---|---|----------|
| RATING  | Operating Temperature Range   | -40°C to +85°C(95%RH max)<br>(note1,2) | Storage Temperature Range   | -30°C to +60°C(95%RH max)<br>(note1)            |          |
|   | Voltage   | 50 V AC / 60 V DC                      | Current   | 1.5 A/pin (all pin)<br>3 A/pin (pin No.1,2,6,7) |          |
| <b>SPECIFICATIONS</b>   |   |  |   |   |          |
| ITEM  | TEST METHOD   |  | REQUIREMENTS  | QT  | AT       |
| <b>CONSTRUCTION</b>   |   |  |   |   |          |
| General Examination   | Examined visually and with a measuring instrument.  |  | According to drawing.   | X   | X        |
| Marking   | Confirmed visually.   |  | According to drawing.   | X   | X        |
| <b>ELECTRIC CHARACTERISTICS</b>   |   |  |   |   |          |
| Contact Resistance  | Measured at 100 mA max (DC or 1000 Hz).   |  | Contact : 30 mΩ max. (note3)<br>Shield : 100 mΩ max. (note3)  | X   | —        |
| Insulation Resistance   | Measured at 500 V DC.   |  | 500 MΩ min.   | X   | —        |
| Voltage Proof   | 500 V DC applied for 1 min. Current leakage 2mA max.  |  | No flashover or breakdown.  | X   | —        |
| Insertion Loss  | Measured in the range of 1 to 500 MHz.  |  | 0.02 √(f) dB max.<br>(Whenever the formula results in a value less than 0.1 dB, the requirement shall revert to 0.1 dB.)  | X   | —        |
| Return Loss   | Measured in the range of 1 to 500 MHz.  |  | 68 – 20log(f) dB min.<br>(Whenever the formula results in a value greater than 30 dB, the requirement shall revert to 30 dB.)   | X   | —        |
| Near end Crosstalk  | Measured in the range of 1 to 500 MHz.  |  | 94 – 20log(f) dB min. (1MHz to 250MHz)<br>46.04 – 30log(f/250) dB min. (250MHz to 500MHz)<br>(Whenever the formula results in a value greater than 75 dB, the requirement shall revert to 75 dB.) | X   | —        |
| Far end crosstalk   | Measured in the range of 1 to 500 MHz.  |  | 83.1 – 20log(f) dB min.<br>(Whenever the formula results in a value greater than 75 dB, the requirement shall revert to 75 dB.)   | X   | —        |
| Transverse Conversion Loss  | Measured in the range of 1 to 500 MHz.  |  | 68 – 20log(f) dB min.<br>(Whenever the formula results in a value greater than 50 dB, the requirement shall revert to 50 dB.)   | X   | —        |
| Transverse Conversion Transfer Loss   | Measured in the range of 1 to 500 MHz.  |  | 68 – 20log(f) dB min.<br>(Whenever the formula results in a value greater than 50 dB, the requirement shall revert to 50 dB.)   | X   | —        |
| <b>MECHANICAL CHARACTERISTICS</b>   |   |  |   |   |          |
| Insertion and Withdrawal Forces   | A maximum rate of 50 mm/min.<br>Measured by applicable connector.                                     |  | Insertion force 25 N max.<br>Withdrawal force 25 N max.   | X   | —        |
| Mechanical Operation  | 5000 times insertions and extractions.<br><br>Mating speed : 10 mm/s max.<br>Rest : 5s, min.(unmated) |  | 1) Resistance:<br>Contact : 80 mΩ max. (note3)<br>Shield : 100 mΩ max. (note3)<br>2) No damage, cracks or looseness of parts.   | X   | —        |
| <b>Note</b>   |   |  |   |   |          |
| 1. Non-condensing. 2. The operation temperature includes the temperature rise by current carrying<br>3. The cable conductor resistance is not considered.<br>4. Electrical characteristics are applicable to the contacts and shield except for contacts No. 3 and 8. |   |  |   |   |          |
|   | COUNT   | DESCRIPTION OF REVISIONS               | DESIGNED  | CHECKED   | DATE     |
|   | 18  | DIS-E-00003730                         | MT.YASUDA   | KI.KAGOTANI                                     | 20210317 |
| REMARK  |   |  | APPROVED  | RI.TAKAYASU                                     | 20180730 |
|   |   |  | CHECKED   | KI.NAGANUMA                                     | 20180727 |
|   |   |  | DESIGNED  | JY.IGA  | 20180727 |
| Unless otherwise specified, refer to IEC 60512.   |   |  | DRAWN   | JY.IGA  | 20180727 |
| Note  | QT:Qualification Test AT:Assurance Test X:Applicable Test   |  | DRAWING NO.   | ELC-129830-00-00                                |          |
|   | SPECIFICATION SHEET   |  | PART NO.  | IX32G-B-8S-CV(7.0)                              |          |
|   | HIROSE ELECTRIC CO., LTD.   |  | CODE NO.  | CL0251-0043-0-00                                | 1/3      |

Jul.1.2022 Copyright 2022 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

| SPECIFICATIONS   |  |   |                              |                    |       |
|--|--|---|------------------------------|--------------------|-------|
| ITEM   | TEST METHOD  | REQUIREMENTS  | QT                           | AT                 |       |
| △<br>Vibration ,sinusoidal                                     | Frequency 10 to 500 Hz<br>0.35 mm, 50 m/s <sup>2</sup><br>2hrs in each of 3 mutually perpendicular axis.   | △<br>1) No electrical discontinuity of 1μs. (note4)<br>2) No damage, cracks or looseness of parts.  | X                            | —                  |       |
| Fretting Corrosion   | 490 m/s <sup>2</sup> , 30 times/min at 1000 times.   | △<br>1) No electrical discontinuity of 1μs. (note4)<br>2) No damage, cracks or looseness of parts.  | X                            | —                  |       |
| △<br>Mechanical Shock  | Subject mated specimens to 300 m/s <sup>2</sup> half-sine shock pulses of 11 milliseconds duration, 3 shocks in both directions of 3 mutually perpendicular directions (totally 18 shocks) | △<br>1) No electrical discontinuity of 1μs. (note4)<br>2) Resistance:<br>Contact : 80 mΩ max. (note4)<br>Shield : 100 mΩ max. (note4)<br>3) No damage, cracks or looseness of parts.  | X                            | —                  |       |
| △<br>Effectiveness of the connector coupling device            | Applying 80 N force for the mating axis direction in state in fitted with applicable connector.  | No unlocking, damage, cracks or looseness of parts.   | X                            | —                  |       |
| △<br>Locking device mechanical operations                      | 10000 cycles<br>20 cycles/min max  | 1) Insertion and Withdrawal Forces<br>Insertion force 25 N max.<br>Withdrawal force 25 N max.<br>2) No damage, cracks or looseness of parts.  | X                            | —                  |       |
| Wrenching Strength   | Applying 25times of 30 N 1s for 2 axis direction on tip of plug case in state in fitted with applicable connector.   | No damage, cracks or looseness of parts.  | X                            | —                  |       |
| ENVIRONMENTAL CHARACTERISTICS                                  |  |   |                              |                    |       |
| Rapid Change of Temperature<br>△                               | Subject mated specimens to 10 cycles between -55°C and 85°C with 30 minutes dwell at temp. extremes and 2 to 3 minutes transition between temperatures.                                    | △<br>1) Voltage proof : 500 V DC applied for 1 min.<br>Current leakage 2mA max.<br>No flashover or breakdown.<br>2) Resistance:<br>Contact : 80 mΩ max. (note3)<br>Shield : 100 mΩ max. (note3)<br>3) Insulation resistance: 500 MΩ min. (at dry)<br>4) No damage, cracks or looseness of parts.  | X                            | —                  |       |
| Humidity / Temperature Cycling                                 | Low temperature 25 °C;<br>High temperature 65 °C;<br>Cold sub-cycle - 10 °C;<br>Relative humidity 93 %<br>Duration 10 / each 24 h<br>(IEC 60068-2-38,test Z / AD)                          | △<br>1) Voltage proof : 500 V DC applied for 1 min.<br>Current leakage 2mA max.<br>No flashover or breakdown.<br>2) Resistance:<br>Contact : 80 mΩ max. (note3)<br>Shield : 100 mΩ max. (note3)<br>3) Insulation resistance: 500 MΩ min. (at dry)<br>4) Insertion and Withdrawal Forces<br>Insertion force 25 N max.<br>Withdrawal force 25 N max.<br>5) No damage, cracks or looseness of parts. | X                            | —                  |       |
| Damp Heat, Steady State  | Subject mated specimens to a relative humidity of 93 % at a temperature of 40°C during 21 days.  | △<br>1) Voltage proof : 500 V DC applied for 1 min.<br>Current leakage 2mA max.<br>No flashover or breakdown.<br>2) Resistance:<br>Contact : 80 mΩ max. (note3)<br>Shield : 100 mΩ max. (note3)<br>3) Insulation resistance: 500 MΩ min. (at dry)<br>4) Insertion and Withdrawal Forces<br>Insertion force 25 N max.<br>Withdrawal force 25 N max.<br>5) No damage, cracks or looseness of parts. | X                            | —                  |       |
| Note QT:Qualification Test AT:Assurance Test X:Applicable Test |  |   | DRAWING NO. ELC-129830-00-00 |                    |       |
| <b>HRS</b>   | SPECIFICATION SHEET  |   | PART NO.                     | IX32G-B-8S-CV(7.0) |       |
|  | HIROSE ELECTRIC CO., LTD.  |   | CODE NO                      | CL0251-0043-0-00   | △ 2/3 |

Jul.1.2022 Copyright 2022 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

| SPECIFICATIONS  |  |  |             |                    |   |
|---|--|--|-------------|--------------------|---|
| ITEM  | TEST METHOD  | REQUIREMENTS   | QT          | AT                 |   |
| <b>ENVIRONMENTAL CHARACTERISTICS</b>  |  |  |             |                    |   |
| Dry Heat  | Subject to +85 ± 2 °C, 21 days.<br>(mating applicable connector)   |  1) Voltage proof : 500 V DC applied for 1 min.<br>Current leakage 2mA max.<br>No flashover or breakdown.<br>2) Resistance:<br>Contact : 80 mΩ max. (note3)<br>Shield : 100 mΩ max. (note3)<br>3) Insulation resistance: 500 MΩ min. (at dry)<br>4) Insertion and Withdrawal Forces<br>Insertion force 25 N max.<br>Withdrawal force 25 N max.<br>5) No damage, cracks or looseness of parts. | X           |                    | —   |
| Cold  | Subject to -55 ± 3 °C, 10 days.<br>(mating applicable connector)   |  1) Voltage proof : 500 V DC applied for 1 min.<br>Current leakage 2mA max.<br>No flashover or breakdown.<br>2) Resistance:<br>Contact : 80 mΩ max. (note3)<br>Shield : 100 mΩ max. (note3)<br>3) Insulation resistance: 500 MΩ min. (at dry)<br>4) Insertion and Withdrawal Forces<br>Insertion force 25 N max.<br>Withdrawal force 25 N max.<br>5) No damage, cracks or looseness of parts. | X           |                    | —   |
| Corrosion Salt Mist   | Subject to 5 % salt water, 35 ± 2 °C, 48h.<br>(leave under unmated condition.)   | No heavy corrosion of contacts.  | X           |                    | —   |
| Mixed Flowing Gas Corrosion   | Test temperature : +25±1 °C, Relative humidity : 75±3 %<br>H <sub>2</sub> S : 10±5 ppb, NO <sub>2</sub> : 200±50 ppb<br>Cl <sub>2</sub> : 10±5 ppb, SO <sub>2</sub> : 200±20 ppb<br>Leave the samples for 4 days with mated.<br>The same is performed with unmated samples.<br>(IEC 60512, method 4) |  1) Resistance:<br>Contact : 80 mΩ max. (note3)<br>Shield : 100 mΩ max. (note3)<br>2) No damage, cracks or looseness of parts.  | X           |                    | —   |
|   |  |  |             |                    |   |
| Note QT:Qualification Test AT:Assurance Test X:Applicable Test                      |  |  | DRAWING NO. |                    | ELC-129830-00-00  |
|  | SPECIFICATION SHEET  |  | PART NO.    | IX32G-B-8S-CV(7.0) |   |
|   | HIROSE ELECTRIC CO., LTD.  |  | CODE NO     | CL0251-0043-0-00   |  3/3 |