


APPLICABLE STANDARD							
RATING	OPERATING TEMPERATURE RANGE	-40°C TO +85°C(95%RH MAX)		STORAGE TEMPERATURE RANGE	-40°C TO +85°C(95%RH MAX)		
	POWER	_____ W		CHARACTERISTIC IMPEDANCE	50Ω ( 0 TO $\Delta$ 8GHz)		
	PECULIARITY	_____		APPLICABLE CABLE	_____		
SPECIFICATIONS							
ITEM		TEST METHOD		REQUIREMENTS		QT	AT
CONSTRUCTION							
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.		×	×
MARKING		CONFIRMED VISUALLY.				-	-
ELECTRIC CHARACTERISTICS							
CONTACT RESISTANCE		mA MAX (DC OR 1000 Hz).		CENTER CONTACT	mΩ MAX.	-	-
				OUTER CONTACT	mΩ MAX.	-	-
INSULATION RESISTANCE		250 V DC		500	MΩ MIN.	×	-
VOLTAGE PROOF		300 V AC FOR 1 min.CURRENT LEAKAGE 2mA MAX.		NO FLASHOVER OR BREAKDOWN.		×	-
VOLTAGE STANDING WAVE RATIO		FREQUENCY 0.045 TO 6 GHz.		VSWR 1. 2 MAX.		×	-
$\Delta$		FREQUENCY 6 TO 8 GHz.		VSWR 1. 3 MAX.			
INSERTION LOSS		FREQUENCY TO GHz		dB MAX.		-	-
MECHANICAL CHARACTERISTICS							
CONTACT INSERTION AND EXTRACTION FORCES		MEASURED BY $\phi 0.9017 \begin{smallmatrix} 0 \\ -0.0025 \end{smallmatrix}$ STEEL GAUGE.		INSERTION FORCE	N MAX.	-	-
				EXTRACTION FORCE	0.3 N MIN.	×	-
INSERTION AND EXTRACTION FORCES		MEASURED BY APPLICABLE CONNECTOR.		INSERTION FORCE	N MAX.	-	-
				EXTRACTION FORCE	N MAX.	-	-
MECHANICAL OPERATION (U.FL SIDE)		10000 TIMES INSERTIONS AND EXTRACTIONS. (400-600 cycles per hour)		1) NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		×	-
VIBRATION		FREQUENCY TO Hz SINGLE AMPLITUDE mm, m/s <sup>2</sup> AT CYCLES FOR DIRECTIONS.		1) NO ELECTRICAL DISCONTINUITY OF $\mu$ s. 2) NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		-	-
SHOCK		m/s <sup>2</sup> DIRECTIONS OF PULSE ms AT TIMES FOR DIRECTIONS.				-	-
CABLE CLAMP ROBUSTNESS (AGAINST CABLE PULL)		APPLYING A PULL FORCE THE CABLE AXIALLY AT N MAX.		1) NO WITHDRAWAL AND BREAKAGE OF CABLE. 2) NO BREAKAGE OF CLAMP.		-	-
ENVIRONMENTAL CHARACTERISTICS							
DAMP HEAT,CYCLIC		EXPOSED AT TO °C, ~ % TOTAL CYCLES ( h )		1) INSULATION RESISTANCE: MΩ MIN. (AT HIGH HUMIDITY) 2) INSULATION RESISTANCE: MΩ MIN. (AT DRY) 3) NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		-	-
RAPID CHANGE OF TEMPERATURE		TEMPERATURE → → → °C TIME → → → min. UNDER CYCLES.		NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		-	-
CORROSION SALT MIST		EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.		$\Delta$ VSWR SPEC WITHIN STANDARD		×	-
	COUNT	DESCRIPTION OF REVISIONS		DESIGNED		CHECKED	DATE
$\Delta$	3	DIS-D-00004690		NK. NINOMIYA		TS. NOBE	20200207
REMARK				APPROVED	I.J. MITANI	20050105	
				CHECKED	KY. SHIMIZU	20050105	
				DESIGNED	TO. KATAYAMA	20050105	
Unless otherwise specified, refer to JIS C 5402.				DRAWN	MH. WATANABE	20050105	
Note QT:Qualification Test AT:Assurance Test X:Applicable Test				DRAWING NO.		ELC4-302679-40	
		SPECIFICATION SHEET		PART NO.		HRMJ-U. FLP-ST1 (40)	
		HIROSE ELECTRIC CO., LTD.		CODE NO.		CL311-0385-5-40	$\Delta$ 1/1