

Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


Notes. 1. Recommended cable condition is shown below.
<1> A list of compatible cables is available on the Hirose website.
When using a non-recommended cable, please contact a Hirose sales representative.
Refer to the technical specification (ETAD-E3222) for wiring and assembly procedures.

<1> Recommended Cable <1>

Items	Recommended Condition
Conductor size	AWG # 28-22
Insulation O.D.	φ 1.55 mm MAX.
Braid Shield	Tin plating
Sheath O.D.	φ 6.3 -7.2 mm








HRS DRAWING FOR REFERENCE

<2> This product (Type A) is defined for 10/100 Mbit/s and 1/10 Gbit/s Ethernet communication. Please use Type B for all other non Ethernet applications like signaling, serial or other industrial bus communication systems.

<1> Mating Key



<1><3> Excluding the plug unit, this product is packaged separately by the type of parts.
The shield shell is packaged prior to bending.(See next page.)
Refer to the technical specification (ETAP-E3224) for packing.

NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
4	PA	Black, UL94V-0			
3	Stainless Steel		8	PC	Dark gray, UL94V-0
2	PA	Black, UL94V-0	7	PC	Dark gray, UL94V-0
1	Copper Alloy	Contact area : Gold 0.2 μm min Wiring area : Gold 0.03 μm min Under plating : Nickel 2 μm min	6	Stainless Steel	Nickel 0.2 μm min
			5	Stainless Steel	Nickel 1μm min

UNITS	SCALE		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm	2 : 1	<1>	6	DIS-E-00006884	MT. YASUDA	KI. KAGOTANI	20210929

HIROSE ELECTRIC CO., LTD.

APPROVED	MN. KENJO	20200601
CHECKED	KI. NAGANUMA	20200601
DESIGNED	MT. YASUDA	20200601
DRAWN	MY. KOMUKAI	20200601

DRAWING NO.	EDC-129987-00-00
PART NO.	IX40G-A-10S-CVL1(7.0)
CODE NO.	CL0251-0075-0-00


<1> 1/2

Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demands high reliability, kindly contact our sales window correspondents.


2 Pin Assignment For 10/100 Mbit/s And 1/10 Gbit/s Ethernet

Contact No.	Signal	
	10/100 Mbit/s	1/10 Gbit/s
1	TX+	BI_DA+
2	TX-	BI_DA-
3	N.C	N.C
4	N.C	BI_DC+
5	N.C	BI_DC-
6	RX+	BI_DB+
7	RX-	BI_DB-
8	N.C	N.C
9	N.C	BI_DD+
10	N.C	BI_DD-

3 Shield Shell Delivery Form





3 Product Structure




HRS DRAWING FOR REFERENCE

Plug Unit





1 Mated Condition



HRS	DRAWING NO.	EDC-129987-00-00
	PART NO.	IX40G-A-10S-CVL1(7.0)
	CODE NO.	CL0251-0075-0-00
		1 2/2