

Part No.	Cable color
~066N1~	GRAY
~066N2~	BLACK

NOTE 1 We indicate the length of the harness on the last of product name, 'L' part.


2 Tolerance for [L]

Length L [mm]	Tolerance [mm]
$35 \leq L \leq 200$	± 4
$200 < L \leq 500$	± 8
$500 < L \leq 1000$	± 12
$1000 < L$	$\pm 1.5\%$

3 Connector rotation angle is within ± 45 degree from the above image.
For long length in the case of $L > 500$, the angle is optional.

4. Specifications are subject to change without notice.


[DIMENSIONS OF CONNECTOR]







For stable supply of this series,
material supplier of piece part#1
will be changed during 2019-2022.
Please note this change in advance.
There will be no difference in product
performance and quality.

[PRECAUTIONS FOR HANDLING]

- ◆ Connector insertion and extraction
 - a. Connector shall be extracted vertically by specialised extraction JIG.
Part No.: H.FL-LP-NCCL Code: CL331-0551-7)
Never hold the cable when extracting the cable because it damages the connector.
 - b. Insert the connector as perpendicularly to the mating surface as possible by aligning the mating axes of both connectors. Do not excessively slant the connectors when inserting.



2	H. FL-LP CONTACT	CL331-0511-2					
1	H. FL-LP-A32-A(C01)	CL331-0508-8-01		3	1.32Dia. coaxial cable		
NO.	PART NO.	CODE NO.		NO.	PART NO.		
UNITS mm		SCALE FREE	 COUNT 1	DESCRIPTION OF REVISIONS DIS-D-00003994	DESIGNED MK. INOUE	CHECKED NK. NINOMIYA	DATE 20190419
 HIROSE ELECTRIC CO., LTD.		APPROVED : NK. NINOMIYA		20180608	DRAWING NO.		
		CHECKED : MT. KANEKO		20180608	PART NO.		
		DESIGNED : MS. MATSUMOTO		20180608	H. FL-2LP(A)-066**-A-L  1		
		DRAWN : MS. MATSUMOTO		20180608	CODE NO.		
			