




Applicable standard					
Rating	Operating temperature range	-55°C to +125 °C (95 %RH Max.)	Storage temperature range	-55 °C to +125 °C (95 %RH Max.)	
	Power	-- W	Characteristic impedance	50 Ω (0 to 65 GHz)	
	Peculiarity	----	Applicable cable	----	
SPECIFICATIONS					
ITEM	TEST METHOD		REQUIREMENTS	QT	AT
CONSTRUCTION					
General examination	Visually and by measuring instrument.		According to drawing.	X	X
Marking	Confirmed visually.			-	-
ELECTRICAL CHARACTERISTICS					
Contact resistance	100 mA Max.(DC or 1000 Hz)		Center contact 16 mΩ Max.	X	X
			Outer contact 16 mΩ Max.	X	X
Insulation resistance	250 V DC.		500 MΩ Min.	X	X
Withstanding voltage	250 V AC for 1 min. current leakage 2 mA Max.		No flashover or breakdown.	X	X
Return loss	Frequency 0 to 40 GHz.		Return loss 15 dB Min.	X	X
	Frequency 40 to 65 GHz.		Return loss 10 dB Min.		
Insertion loss	Frequency - to - GHz.		--- dB Max.	-	-
MECHANICAL CHARACTERISTICS					
Contact insertion and extraction forces	--- by steel gauge.		Insertion force --- N Max.	-	-
			Extraction force --- N Min.	-	-
Insertion and extraction forces	Measured by applicable connector.		Insertion force --- N Max.	-	-
			Extraction force --- N Min.	-	-
Mechanical operation	500 times insertion and extractions.		1)Contact resistance: Center contact 28 mΩ Max. Outer contact 28 mΩ Max. 2)No damage, crack and looseness of parts.	X	-
Vibration	Frequency 10 to 500 Hz single amplitude 0.75 mm, 98 m/s ² at 10 cycles for 3 directions.		1)No electrical discontinuity of 1 μs. 2)No damage, crack and looseness of parts.	X	-
Shock	490 m/s ² directions of pulse 11 ms at 3 times for 3 directions.			X	-
Cable clamp strength (Against cable pull)	Using a pulling tester, pull the cable axially at a rate of -- mm/min. and record the strength at which the cable or connector breaks.		--- N Min.	-	-
ENVIRONMENTAL CHARACTERISTICS					
Damp heat	Exposed at -10 to +65 °C, 90 to 98 % total 10 cycles.(240 h)		1)Insulation resistance: 100 MΩ Min. (at high humidity) 2) Insulation resistance: 500 MΩ Min. (at dry) 3)No damage, crack and looseness of parts.	X	-
Rapid change of temperature	Temperature -65 → - → +125 → - °C Time 30 → 3 → 30 → 3 min. Under 5 cycles.		No damage, crack and looseness of parts.	X	-
Corrosion salt mist	Exposed in 5 % salt water spray for 48 h.		Return loss 15 dB Min. (Frequency 0 ~ 40 GHz.) Return loss 10 dB Min. (Frequency 40 ~65 GHz.)	X	-
	Count	Description of revisions	Designed	Checked	Date
Remark RoHS COMPLIANT			Approved	KY.SHIMIZU	16.02.09
			Checked	TO.KATAYAMA	16.02.09
			Designed	YI.FUNADA	16.02.09
			Drawn	YI.FUNADA	16.02.09
Unless otherwise specified, refer to IEC 60512.					
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			Drawing No.	ELC-313092-00-00	
	SPECIFICATION SHEET		Part No.	SMPMP(SB)-HVP	
	HIROSE ELECTRIC CO., LTD.		Code No.	CL311-0420-4-00	 1/1