









1	2	3	4																																											
A				A																																										
B	<table border="1" data-bbox="1037 627 1348 761"><thead><tr><th>Part No.</th><th>Cable color</th></tr></thead><tbody><tr><td>~04*1TV~</td><td>WHITE</td></tr><tr><td>~04*2TV~</td><td>BLACK</td></tr></tbody></table>			Part No.	Cable color	~04*1TV~	WHITE	~04*2TV~	BLACK	B																																				
Part No.	Cable color																																													
~04*1TV~	WHITE																																													
~04*2TV~	BLACK																																													
C	<p>NOTE 1 We indicate the length of the harness on the last of product name, 'L' part.</p> <p>2 Tolerance for [L]</p> <table border="1" data-bbox="454 1041 1061 1243"><thead><tr><th>Length L [mm]</th><th>Tolerance [mm]</th></tr></thead><tbody><tr><td>$35 \leq L \leq 200$</td><td>± 4</td></tr><tr><td>$200 < L \leq 500$</td><td>± 8</td></tr><tr><td>$500 < L \leq 1000$</td><td>± 12</td></tr><tr><td>$1000 < L$</td><td>$\pm 1.5\%$</td></tr></tbody></table>			Length L [mm]	Tolerance [mm]	$35 \leq L \leq 200$	± 4	$200 < L \leq 500$	± 8	$500 < L \leq 1000$	± 12	$1000 < L$	$\pm 1.5\%$	C																																
Length L [mm]	Tolerance [mm]																																													
$35 \leq L \leq 200$	± 4																																													
$200 < L \leq 500$	± 8																																													
$500 < L \leq 1000$	± 12																																													
$1000 < L$	$\pm 1.5\%$																																													
D	<p>3. Specifications are subject to change without notice.</p>			D																																										
E	<p>【 DIMENSIONS OF CONNECTOR 】</p>  <div data-bbox="917 1624 1404 1848"><p>For stable supply of this series, material supplier of piece part#1 will be changed during 2019-2022. Please note this change in advance. There will be no difference in product performance and quality.</p></div>			E																																										
F	<table border="1" data-bbox="183 1870 1508 2161"><thead><tr><th>1</th><th>W.FL-LP-040HF(06)</th><th>CL331-0563-6-06</th><th>2</th><th>0.81 Dia. coaxial cable</th><th>HALOGEN FREE</th></tr><tr><th>NO.</th><th>PART NO.</th><th>CODE NO.</th><th>NO.</th><th>PART NO.</th><th></th></tr></thead><tbody><tr><td>UNITS mm</td><td></td><td>SCALE FREE</td><td>COUNT </td><td>DESCRIPTION OF REVISIONS</td><td>DESIGNED</td></tr><tr><td colspan="2">HIROSE ELECTRIC CO., LTD.</td><td>APPROVED : NK. NINOMIYA</td><td>20181128</td><td>DRAWING NO.</td><td></td></tr><tr><td colspan="2"></td><td>CHECKED : MT. KANEKO</td><td>20181128</td><td>PART NO.</td><td>WFL-LPHF6-04**TV-A-L</td></tr><tr><td colspan="2"></td><td>DESIGNED : MS. MATSUMOTO</td><td>20181128</td><td>CODE NO.</td><td></td></tr><tr><td colspan="2"></td><td>DRAWN : MK. INOUE</td><td>20181128</td><td></td><td></td></tr></tbody></table>			1	W.FL-LP-040HF(06)	CL331-0563-6-06	2	0.81 Dia. coaxial cable	HALOGEN FREE	NO.	PART NO.	CODE NO.	NO.	PART NO.		UNITS mm		SCALE FREE	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED	HIROSE ELECTRIC CO., LTD.		APPROVED : NK. NINOMIYA	20181128	DRAWING NO.				CHECKED : MT. KANEKO	20181128	PART NO.	WFL-LPHF6-04**TV-A-L			DESIGNED : MS. MATSUMOTO	20181128	CODE NO.				DRAWN : MK. INOUE	20181128			F
1	W.FL-LP-040HF(06)	CL331-0563-6-06	2	0.81 Dia. coaxial cable	HALOGEN FREE																																									
NO.	PART NO.	CODE NO.	NO.	PART NO.																																										
UNITS mm		SCALE FREE	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED																																									
HIROSE ELECTRIC CO., LTD.		APPROVED : NK. NINOMIYA	20181128	DRAWING NO.																																										
		CHECKED : MT. KANEKO	20181128	PART NO.	WFL-LPHF6-04**TV-A-L																																									
		DESIGNED : MS. MATSUMOTO	20181128	CODE NO.																																										
		DRAWN : MK. INOUE	20181128																																											
FORM HC0011-5-51																																														