Feb.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

Applicable standard				
Rating	Operating temperature range	-40 ℃ to +105 ℃(90 %RH Max.)	Storage temperature range	-40 ℃ to +90 ℃(90 %RH Max.)
	Power	- W	Characteristic impedance	50 Ω(0 to 8 GHz)
	Peculiarity	-	Applicable cable	0.81 Dia. coaxial cable.

SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION				
General examination	Visually and by measuring instrument.	According to drawing.	X	X
ELECTRICAL CHARACTERISTICS				
Insulation resistance	100 V DC.	500 MΩ Min.	X	X
Withstanding voltage	200 V AC for 1 min. current leakage 2 mA Max.	No breakdown.	X	X
Voltage standing wave ratio 1	Frequency 0 to 3 GHz.	VSWR 1.3 Max.	X	-
	Frequency 3 to 6 GHz.	VSWR 1.4 Max.		
	Frequency 6 to 8 GHz.	VSWR 1.5 Max.		
MECHANICAL CHARACTERISTICS				
Cable clamp strength (Against cable pull)	Using a pulling tester, pull the cable axially at a rate of 10 mm/min. and record the strength at which the cable or connector breaks.	7 N Min.	X	-

	Count	Description of revisions	Designed	Checked	Date
2	1	DIS-D-00011757	MS.MATSUMOTO	MT.KANEKO	20220510

Remark HALOGEN FREE

Notes 1 VSWR is measured with SMA conversion adapters attached to both ends of the applicable cable assembled.

2. "L" at the end of the product name indicates the cable length (unit:mm).

3. Specifications are subject to change without notice.

Unless otherwise specified, refer to IEC 60512. 2

Approved	NK.NINOMIYA	20160726
Checked	MT.KANEKO	20160726
Designed	MS.MATSUMOTO	20160726
Drawn	MS.MATSUMOTO	20160726

Note QT:Qualification Test AT:Assurance Test X:Applicable Test

		Drawing No.	
HRS	SPECIFICATION SHEET	Part No.	WFL2-2LPHF6-04**TV-A-L
	HIROSE ELECTRIC CO., LTD.	Code No.	2 1/1

FORM HD0011-2-1