

Jun.1.2021 Copyright 2021 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

Applicable standard					
Rating	Operating temperature range	-40 °C to +90 °C(90 %RH Max.)	Storage temperature range	-40 °C to +90 °C(90 %RH Max.)	
	Power	-- W	Characteristic impedance	50 Ω(0 to 6 GHz)	
	Peculiarity	----	Applicable cable	0.81 Dia. coaxial cable.	
SPECIFICATIONS					
ITEM	TEST METHOD		REQUIREMENTS	QT	AT
CONSTRUCTION					
General examination	Visually and by measuring instrument.		According to drawing.	X	X
ELECTRICAL CHARACTERISTICS					
Insulation resistance	100 V DC.		500 MΩ Min.	X	X
Withstanding voltage	200 V AC for 1 min. current leakage 2 mA Max.		No flashover or breakdown.	X	X
Voltage standing wave ratio	<input type="checkbox"/> Frequency 0 to 3 GHz. <input type="checkbox"/> Frequency 3 to 6 GHz.		VSWR 1.3 Max. VSWR 1.4 Max.	X	—
MECHANICAL CHARACTERISTICS					
Cable clamp strength (Against cable pull)	Using a pulling tester, pull the cable axially at a rate of 10 mm/min. and record the strength at which the cable or connector breaks.		7 N Min.	X	—
Count	Description of revisions		Designed	Checked	Date
<input type="checkbox"/>					
Remark			Approved	NK.NINOMIYA	16.07.26
NOTE <input type="checkbox"/> VSWR was measured with SMA conversion adapters attached to both ends of the applicable cable assembled			Checked	MT.KANEKO	16.07.26
2. Specifications are subject to change without notice.			Designed	MS.MATSUMOTO	16.07.26
HALOGEN FREE			Drawn	MS.MATSUMOTO	16.07.26
Unless otherwise specified, refer to IEC 60512.					
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			Drawing No.		
HRS	SPECIFICATION SHEET		Part No. WFL2-2LPHF6-04**TV-A-L		
	HIROSE ELECTRIC CO., LTD.		Code No.		
					<input type="checkbox"/> 1/1