

1		2		3		4											
A		B		C		D											
		<table border="1"><thead><tr><th>Part No.</th><th>Cable color</th></tr></thead><tbody><tr><td>~04*1TV~</td><td>WHITE</td></tr><tr><td>~04*2TV~</td><td>BLACK</td></tr></tbody></table>						Part No.	Cable color	~04*1TV~	WHITE	~04*2TV~	BLACK				
Part No.	Cable color																
~04*1TV~	WHITE																
~04*2TV~	BLACK																
NOTE		<p>① We indicate the length of the harness on the last of product name, 'L' part.</p> <p>② Tolerance for [L]</p> <table border="1"><thead><tr><th>Length L [mm]</th><th>Tolerance [mm]</th></tr></thead><tbody><tr><td>$35 \leq L \leq 200$</td><td>± 4</td></tr><tr><td>$200 < L \leq 500$</td><td>± 8</td></tr><tr><td>$500 < L \leq 1000$</td><td>± 12</td></tr><tr><td>$1000 < L$</td><td>$\pm 1.5\%$</td></tr></tbody></table> <p>③ Connector rotation angle is within ± 45 degree from the above image. For long length in the case of $L > 500$, the angle is optional.</p> <p>4. Specifications are subject to change without notice.</p>						Length L [mm]	Tolerance [mm]	$35 \leq L \leq 200$	± 4	$200 < L \leq 500$	± 8	$500 < L \leq 1000$	± 12	$1000 < L$	$\pm 1.5\%$
Length L [mm]	Tolerance [mm]																
$35 \leq L \leq 200$	± 4																
$200 < L \leq 500$	± 8																
$500 < L \leq 1000$	± 12																
$1000 < L$	$\pm 1.5\%$																
【 DIMENSIONS OF CONNECTOR 】																	
1		W. FL2-LP-040HF(06)		CL331-0311-3-06		2											
NO.		PART NO.		CODE NO.		NO.											
UNITS mm				SCALE FREE		COUNT 1											
DESCRIPTION OF REVISIONS		DESIGNED		CHECKED		DATE											
DIS-D-00003244		MS. MATSUMOTO		MT. KANEKO		18. 06. 14											
APPROVED : NK. NINOMIYA		16. 07. 26		DRAWING NO.		PART NO.											
CHECKED : MT. KANEKO		16. 07. 26		WFL2-2LPHF6-04**TV-A-L		①											
DESIGNED : MS. MATSUMOTO		16. 07. 26		CODE NO.		①											
DRAWN : MS. MATSUMOTO		16. 07. 26				①											

HIROSE ELECTRIC CO., LTD.

FORM HC0011-5-51

2

3

4