



May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.




VIEW B(20:1)




- NOTE 1 LEAD CO-PLANARITY INCLUDING REINFORCED METAL FITTINGS SHALL BE 0.1MAX.
2 TO BE DELIVERED WITH TAPE AND REEL PACKAGES.

訂正事項					訂正事項				
△數	DESCRIPTION OF REVISIONS	B	Y	CHKD	年月日	△數	DESCRIPTION OF REVISIONS	B	Y
COUNT					DATE	COUNT			
1	-	RE-5-1603	LSG	JDH	17. 03 . 09	4	3	RE-5-2408	OCU
2	1	RE-5-1720	OCU	JDH	17. 07 . 13	5	3	RE-5-2459	OCU
3	-	RE-5-1833	OCU	CDH	17. 12 . 04				

RECOMMENDED LAND PATTERN, METAL MASK (FREE)
RECOMMENDED METAL MASK THICKNESS: t=0.10




△5 RECOMMENDED FFC/FPC (FREE)




			4	PHOSPHOR BRONZE	TIN PLATING 1μm MIN. OVER NICKEL 1μm MIN.								
2	LCP	BLACK	UL94V-0	3	PHOSPHOR BRONZE	(CONTACT AREA) GOLD 0.05μm MIN OVER NICKEL 1μm MIN							
1	LCP	BLACK	UL94V-0			(LEAD) GOLD 0.05μm MIN OVER NICKEL 1μm MIN							
NO.		MATERIAL		FINISH,REMARKS		NO.		MATERIAL		FINISH,REMARKS			
CODE NO. (OLD)				DRAWN		DESIGNED		CHECKED		APPROVED		RELEASED	
				<div>OH</div> <div>17.03.07</div> <div>C.U</div>		<div>OH</div> <div>17.03.07</div> <div>C.U</div>		<div>CHO</div> <div>17.03.07</div> <div>D.H</div>		<div>SONG</div> <div>17.03.07</div> <div>H.C</div>		<div>ENG</div> <div>21.01.20</div> <div>DEPT</div>	
		DRAWING NO.				PART NO.		TF13BA-Series (800)					
SCALE		EDC3-632308-80				CODE NO		CL 6508-0036-0-800					
10:1													
UNITS		HRS HIROSE KOREA CO.,LTD.				1/4							
mm													

May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


EMBOSS CARRIER TAPE DIMENSION



REEL DIMENSION(FREE)



HRS DRAWING FOR REFERENCE



NOTE 1. 1REEL CONTAINS 5,000PCS.


PART NUMBER	NUMBER OF CONTACTS	DIMENSION OF CONNECTOR/ FPC, PCB MOUNTING PATTERN						DIMENSION OF PACKING			
		A	B	C	D	E	F	G	H	I	J
TF13BA-6S-0.4SH(800)	6	2.0	4.2	3.05	3.83	3.0	2.3	4.4	7.5	16.0	16.5
TF13BA-9S-0.4SH(800)	9	3.2	5.4	4.25	5.03	4.2	3.5	5.6	7.5	16.0	16.5
TF13BA-10S-0.4SH(800)	10	3.6	5.8	4.65	5.43	4.6	3.9	6.0	7.5	16.0	16.5

May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

This connector requires dslicate and careful handing.
Read through the instructions shown below and the connector properly.
Each values indicating here are for reference and may differ from standard value.


[INSTRUCTIONS FOR MOUNTING ON THE BOARD]

- ⚠ ◆ Warp of Board
Minimize warp of the board as possible
Lead co-planarity including reinforced metal fitting is 0.1mm or less
Too much warp of the board may result in a soldering problem.
- ◆ Load to Connector
Do not apply a force of 0.5N or more to the connector before mounting it on the board.
Otherwise, the connector may be broken.
Do not warp the FPC or operate the connector before mounting it.
- ◆ Load to board
°Splitting a large board into seveal pieces
°Screwing the board
Avoid the handling described above so that no force is exerted on the board during the assembly process.
Otherwise, the connector may become defective.
- ◆ Amount of Warp
The warp of a 100-mmwide board should be 0.5mm or less.
The warp of board suffers stress on connector and connector may become defective.




[INSTRUCTIONS ON INSERTING FFC/FPC AND CONNECTOR]

- ◆ Use of the Actuator
1. Be very careful not to apply excessive force when releasing the Actuator.
in the initial position (with no FFC/FPC inserted)
if you use your nail or finger as shown, the terimals may be deformed.





- 2. The actuator rotates around the rotational axis as shown below.
Please rotate the actuator.




- 3. Please do not push downwards to the Actuator with more than 0.5N force, as shown below.
Otherwise, the Actuator may fall off or be damaged.

- 4. The actuator will not open more than 100°.
Do not apply any force backward beyond this point.
Otherwise the actuator may come off or braek.



5. Move the actuator at approximately the center.
(It may break if operate the edge of the actuator with FFC/FPC inserted.)
6. Do not pinch or pick the actuator to lift it as shown below, Otherwise, it may break.
(Do not carry out any operation other than rotating the actuator as shown in 2 above.)




◆ Direction of Contacts

This connector has contacts on the bottom. Thus, insert FFC/FPC with the exposed conductors face down.

△ Inserting the FFC/FPC

1. Insert the FFC/FPC horizontally along the surface and at a right angle to the connector.
Insert it properly to the very end.
If the FFC/FPC is inserted at a slant(incorrectly)
the conductors may short-circuit due to pitch shift or the edge of the FFC/FPC may catch in the terminals.
resulting in deformation of the terminals.
This connector has a ZIF structure and its effective engagement length is 1.87mm
(when the recommended FFC/FPC nominal is used)
Use the actuator carefully to prevent the FFC/FPC from dislocating after inserting it.



2. Do not insert the FFC/FPC diagonally from above
If the FFC/FPC is inserted at a slant (incorrectly) as shown below in the FFC/FPC insertion process,
the FFC/FPC may bend and patterns may break or the FFC/FPC may not insert completely.
resulting in improper conduction.
- # Keep a sufficient FFC/FPC insertion space in the stage of the layout in order to avoid incorrect FFC/FPC insertion.
Besides, it is not difficult to insert FFC/FPC correctly all the way to the end.
Designed the proper layout of parts.
 - # Make adjustments with the FFC/FPC manufacturer for bending performance and breakage resistant.


◆ Checking the Locking Condition

In the locked condition, make sure that actuator is horizontal on board surface.
Do not apply excessive force to it near the 0° position of the actuator.
Otherwise, the terminals may be deformed. (Allowable force:1N or less)

[INSTRUCTION ON FFC/FPC LAYOUT AFTER CONNECTOR]


◆ Load to FFC/FPC

Be very careful not to apply any force to the FFC/FPC after inserting it.
Otherwise, the connector may become unlocked or the FFC/FPC may break.
Fix the FPC, in particular, when loads are applied to it continuously.
Design the FFC/FPC layout with care not to bend it sharply near the insertion opening.



[INSTRUCTIONS ON REMOVING FFC/FPC]

- ◆ Release the actuator at approximately the center.
(It may break if ioperate the edge of the actuator with FFC/FPC inserted.)



[OTHER INSTRUCTIONS]

◆ Instruction on Manual Soldering

- Follow the instructions shown when soldering the connector manually during repair work, etc
1. Do not perform reflow soldering or manual soldering with the FFC/FPC inserted into the connector.
 2. Do not heat the connector excessively. Be very careful not to let the soldering iron contact any parts other than connector leads. Otherwise, the connector may be deformed or melt.
 3. Do not use excessive solder(or flux)
if excessive solder(or flux) is used on the terminals, solder or flux may adhere to the contacts or rotating parts of the actuator, resulting in poor contact or a rotation failure of the actuator.