

Applicable standard					
Rating	Operating temperature range	-55 °C to +125 °C (95 %RH Max.)	Storage temperature range	-55 °C to +125 °C (95 %RH Max.)	
	Power	-- W	Characteristic impedance	50 Ω(0 to 40 GHz)	
	Peculiarity	----	Applicable cable	----	
SPECIFICATIONS					
ITEM		TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION					
General examination		Visually and by measuring instrument.	According to drawing.	X	X
Marking		Confirmed visually.		X	X
ELECTRICAL CHARACTERISTICS					
Contact resistance	100 mA Max.(DC or 1000 Hz)	Center contact	8 mΩ Max.	X	X
		Outer contact	4 mΩ Max.	X	X
Insulation resistance	500 V DC.	1000 MΩ Min.		X	X
Withstanding voltage	500 V AC for 1 min. current leakage 2 mA Max.	No flashover or breakdown.		X	X
Voltage standing wave ratio	Frequency 0 to 18 GHz.	VSWR 1.1 Max.		X	X
	Frequency 18 to 26.5 GHz	VSWR 1.15 Max.			
	Frequency 26.5 to 40 GHz.	VSWR 1.2 Max.			
Insertion loss	Frequency 0 to 40 GHz.	0.03+0.03√f dB Max. f:GHz		X	X
MECHANICAL CHARACTERISTICS					
Contact insertion and extraction forces	φ 0.91 ^{+0.005} ₀ by steel gauge.	Insertion force	--- N Max.	—	—
		Extraction force	0.5 to 4.9 N	X	X
Insertion and extraction forces	Measured by applicable connector.	Insertion force	--- N Max.	—	—
		Extraction force	--- N Min.	—	—
Mechanical operation	1000 times insertion and extractions.	1)Contact resistance: Center contact 12 mΩ Max. Outer contact 8 mΩ Max. 2)No damage, crack and looseness of parts.		X	—
Vibration	Frequency 10 to 2000 Hz single amplitude 0.75 mm, 196 m/s ² at 10 cycles for 3 directions.	1)No electrical discontinuity of 1 μs. 2)No damage, crack and looseness of parts.		X	—
Shock	1960 m/s ² directions of pulse 6 ms at 3 times for 6 directions.			X	—
Cable clamp strength (Against cable pull)	Using a pulling tester, pull the cable axially at a rate of mm/min. and record the strength at which the cable or connector breaks.	N Min.		—	—
ENVIRONMENTAL CHARACTERISTICS					
Damp heat	Exposed at -10 to +65 °C, 90 to 98 % total 10 cycles.(240 h)	1)Insulation resistance: 100 MΩ Min. (at high humidity) 2) Insulation resistance: 1000 MΩ Min. (at dry) 3)No damage, crack and looseness of parts.		X	—
Rapid change of temperature	Temperature -55 → — →+125 → — °C Time 30 → 3 → 30 → 3 min. Under 5 cycles.	No damage, crack and looseness of parts.		X	—
Corrosion salt mist	Exposed in 5 % salt water spray for 48 h.	Electrical characteristic shall be met.		X	—
Count	Description of revisions	Designed	Checked	Date	
△					
Remark			Approved	TO.KATAYAMA	18.05.10
			Checked	KY.SHIMIZU	18.05.10
			Designed	TK.SAWAGUCHI	18.05.10
			Drawn	TK.SAWAGUCHI	18.05.10
Unless otherwise specified, refer to IEC 60512.					
Note QT:Qualification Test AT:Assurance Test X:Applicable Test		Drawing No.	ELC-382712-00-00		
HRS	SPECIFICATION SHEET		Part No.		HK-PA-JJ
	HIROSE ELECTRIC CO., LTD.		Code No.		CL338-0112-0-00
				△	1/1