


APPLICABLE STANDARD		MIL-STD-348B						
RATING	OPERATING TEMPERATURE RANGE	-55°C TO +105°C(95%RH MAX)		STORAGE TEMPERATURE RANGE	-55°C TO +85°C(95%RH MAX)			
	POWER	_____ W		CHARACTERISTIC IMPEDANCE	50 Ω (0 TO 50 GHz)			
	PECULIARITY	_____		APPLICABLE CABLE	_____			
SPECIFICATIONS								
ITEM		TEST METHOD		REQUIREMENTS		QT	AT	
CONSTRUCTION								
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.		×	×	
MARKING		CONFIRMED VISUALLY.				×	×	
ELECTRIC CHARACTERISTICS								
CONTACT RESISTANCE		100 mA MAX (DC OR 1000 Hz).		CENTER CONTACT	4 mΩ MAX.	×	×	
				OUTER CONTACT	2 mΩ MAX.	×	×	
INSULATION RESISTANCE		500 V DC.		5000 MΩ MIN.		×	×	
VOLTAGE PROOF		500 V AC FOR 1 min.CURRENT LEAKAGE 2mA MAX.		NO FLASHOVER OR BREAKDOWN.		×	×	
VOLTAGE STANDING WAVE RATIO		FREQUENCY 0.045 TO 50 GHz.		VSWR	1.35 MAX. (0.045 TO 26.5GHz)	×	×	
1		TEST METHOD IS BACK TO BACK.		VSWR	1.40 MAX. (26.5 TO 40GHz)			
				VSWR	1.45 MAX (40 TO 50GHz)			
INSERTION LOSS		FREQUENCY TO GHz		dB MAX.		—	—	
MECHANICAL CHARACTERISTICS								
CONTACT INSERTION AND EXTRACTION FORCES		EXTRACTION GAUGE: ϕ 0.495 $\begin{smallmatrix} 0 \\ -0.005 \end{smallmatrix}$ STEEL GAUGE.		INSERTION FORCE N MAX.		—	—	
				EXTRACTION FORCE 0.2~2 N MIN.		×	×	
INSERTION AND WITHDRAWAL FORCES		MEASURED BY APPLICABLE CONNECTOR.		INSERTION FORCE N MAX.		—	—	
				EXTRACTION FORCE N MIN.		—	—	
MECHANICAL OPERATION		500 TIMES INSERTIONS AND EXTRACTIONS.		1) CONTACT RESISTANCE: CENTER CONTACT 6 mΩMAX. OUTER CONTACT 4 mΩMAX. 2) NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		×	—	
VIBRATION		FREQUENCY 10 TO 2000 Hz SINGLE AMPLITUDE 0.75 mm, 196 m/s ² AT 10 CYCLES FOR 3 DIRECTIONS.		1) NO ELECTRICAL DISCONTINUITY OF 1 μs. 2) NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		×	—	
SHOCK		980 m/s ² DIRECTIONS OF PULSE 6 ms AT 3 TIMES FOR 3 DIRECTIONS.				×	—	
ENVIRONMENTAL CHARACTERISTICS								
DAMP HEAT,CYCLIC		EXPOSED AT -10 TO +65 °C, 90~98 % TOTAL 10 CYCLES (240 h)		1) INSULATION RESISTANCE: 100 MΩ MIN. (AT HIGH HUMIDITY) 2) INSULATION RESISTANCE: 5000 MΩ MIN. (AT DRY) 3) NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		×	—	
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55 → — → +105 → — °C TIME 30 → 3 → 30 → 3 min. UNDER 5 CYCLES.		NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		×	—	
CORROSION SALT MIST		EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.		NO HEAVY CORROSION.		×	—	
	COUNT	DESCRIPTION OF REVISIONS		DESIGNED		CHECKED		DATE
△								
REMARK				APPROVED		TS. NOBE		18. 04. 25
NOTE 1 MEASUREMENT STATE OF BACK TO BACK				CHECKED		MH. OGUSU		18. 04. 25
PORT1  PORT2				DESIGNED		AH. MARUYAMA		18. 04. 25
UNLESS OTHERWISE SPECIFIED, REFER TO MIL-STD-202.				DRAWN		EDWIN TANG		18. 04. 25
Note QT:Qualification Test AT:Assurance Test X:Applicable Test				DRAWING NO.		ELC-381620-11-00		
HRS		SPECIFICATION SHEET		PART NO.		H2. 4-R-SR2-1 (11)		
		HIROSE ELECTRIC CO., LTD.		CODE NO.		CL338-0607-0-11		△ 1/1