





May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


A
B
C
D
E
F




NOTE
1 . ALL LEAD CO-PLANARITY SHALL BE 0.08mm MAX.
2 . CONTACT PLATING SPECIFICATIONS
CONTACT AREA : GOLD 0.05 μm MIN
SMT LEAD : GOLD 0.05 μm MIN
UNDERPLATING : NICKEL 1 μm MIN
(SURFACE : SEALING)
3 . CAV NO. ARE INDICATED IN APPROX POSITION SHOWN.

	COUNT	DESCRIPTION OF REVISIONS	B	Y	CHKD	DATE		COUNT	DESCRIPTION OF REVISIONS	B	Y	CHKD	DATE
△	6	RE-6-1973	JHK	JHW		20. 08. 25	△						. .
△						. .	△						. .
△						. .	△						. .


ENGAGEMENT FIGURE (50:1)




SIGNAL CONTACT



POWER CONTACT


4	PS	CLEAR (EMBOSSED CARRIER TAPE)			
3	COPPER ALLOY	2			
2	COPPER ALLOY	2	6	PS	BLACK (PLASTIC REEL)
1	LCP	UL94 V-0, BLACK	5	POLYESTER	CLEAR (COVER TAPE)
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
REMARKS				DRAWN	DESIGNED
				H. K. JEON	H. K. JEON
				19. 12. 24	19. 12. 24
				CHECKED	APPROVED
				H. W. JO	H. W. JO
				19. 12. 24	19. 12. 24
				RELEASED	19. 12. 24
CODE NO. (OLD)		DRAWING NO.		PART NO.	
		EDC3-632911-00		BK13C06-32DS/2-0.35V(800)	
SCALE		 HIROSE KOREA CO., LTD.		CODE NO	
10:1				CL 6665-0012-4-800	
UNITS				1/3	
mm					

5 RECOMMENDED PCB LAYOUT




RECOMMENDED METAL MASK DIMENSIONS

METAL MASK THICKNESS : 80 μm



4 RECOMMENDED REFLOW TEMPERATURE PROFILE USING LEAD-FREE SOLDER PASTE.




REFLOW METHOD : N₂ REFLOW
NUMBER OF REFLOW CYCLES : 2 CYCLES MAX.
1) REFLOW TIME
DURATION ABOVE 220°C, 60 SEC MAX.
(PEAK TEMPERATURE : 250°C MAX)
2) PRE-HEAT TIME
PRE-HEAT TEMPERATURE(MIN): 150°C
PRE-HEAT TEMPERATURE(MAX): 180°C
PRE-HEAT TIME: 90-120 SEC.

4. THIS TEMPERATURE PROFILE IS PER THE CONDITIONS SHOWN ABOVE. ADDITIONAL FACTORS SUCH AS SOLDER PASTE TYPE, PCB SIZE AND OTHER MOUNTED COMPONENTS COULD AFFECT THE PROFILE. THEREFORE, A THOROUGH EVALUATION OF MOUNTING CONDITION IS REQUIRED PRIOR TO PRODUCTION. TEMPERATURE IS MEASURED AT CONTACT LEAD.
5. PLEASE CONTACT US IN CASE YOU WILL MAKE DIFFERENT SETTINGS FROM OUR RECOMMENDATION.
6. THIS PRODUCT SATISFIES HALOGEN FREE REQUIREMENTS DEFINED AS 900ppm MAXIMUM CHLORINE, 900ppm MAXIMUM BROMINE, AND 1500ppm MAXIMUM TOTAL OF CHLORINE AND BROMINE.
7. THIS PRODUCT COMPLY WITH RoHS.


	DRAWING NO.	EDC3-632911-00	PART NO.	BK13C06-32DS/2-0.35V(800)
	SCALE	10:1	CODE NO	CL 6665-0012-4-800
	UNITS	mm		2/3

May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


EMBOSSED CARRIER TAPE PACKAGING (5:1)





D-D (5:1)



C-C (5:1)



DIRECTION OF UNREELING




TRAILER


LEADER

10 TAPING(FREE)

STYLE AND DIMENSION OF REEL (FREE)



E (10:1)



DETAIL OF PART No. LABEL

SUPPLIER	HIROSE ELECTRIC CO., LTD.
QUANTITY	20,000
PART NO.	BK13C06-32DS/2-0.35V(800)
CODE NO.	CL 6665-0012-4-800
DATE OF MANUFACTURED	2024.05.01
生産月日	年 月 日
図番	** ** *
品名	BK13C06-32DS/2-0.35V(800)
納入数量	20,000個
納入者	HIROSE KOREA

8 . PER REEL 20,000 CONNECTORS.

9 . THE DIMENSIONS IN PARENTHESES ARE FOR REFERENCE.

10 REFERENCE TO JIS C 0806, IEC-60286-3 (PACKAGING OF COMPONENTS FOR AUTOMATIC HANDLING)

DRAWING NO.	EDC3-632911-00	PART NO.	BK13C06-32DS/2-0.35V(800)
SCALE	10:1	CODE NO.	CL 6665-0012-4-800
UNITS	mm		