

Feb.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

	△数 COUNT	訂正事項 DESCRIPTION OF REVISIONS	擔當 B Y	檢圖 CHKD	年月日 DATE
1	1	RE-5-2227	Y.K.G	C.D.H	19. 07. 24
△					. .
△					. .




RECOMMENDED LAND PATTERN.METAL MASK (NO scale)


RECOMMENDED METAL MASK THICKNESS : t=0.12



RECOMMENDED FPC/FFC TYPE A (3:1)




RECOMMENDED FPC/FFC TYPE B (3:1)



HRS DRAWING FOR REFERENCE

A-A (10:1)



NOTE 1 : REFERENCE IS A.
2 : LEAD CO-PLANARUTY SHALL BE 0.1mm MAX

NO.	MATERIAL	FINISH,REMARKS
4	BRASS	TIN PLATING 1μm MIN, OVER COPPER 0.3μm MIN
3	PHOSPHOR BRONZE	(CONTACT AREA, LEAD) GOLD PLATING 0.03μm MIN, OVER NICKEL 1μm MIN △1 (OTHER) NICKEL PLATING 1μm MIN
2	LCP	UL94V-0, BLACK
1	LCP	UL94V-0, BEIGE

CODE NO. (OLD)	DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
	LEE 17.06.02 S.G	LEE 17.06.02 S.G	CHO 17.06.02 D.H	SONG 17.06.02 H.C	ENG 19.07.24 DEPT.

SCALE 5:1	DRAWING NO. EDC3-632347	PART NO. TF31-**S-0.5SH(895)
UNITS mm	HRS HIROSE KOREA CO.,LTD.	CODE NO CL 6535-0064-8-895 1/5


Feb.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


	△数 COUNT	訂正事項 DESCRIPTION OF REVISIONS	擔當 B Y	檢圖 CHKD	年月日 DATE		△数 COUNT	訂正事項 DESCRIPTION OF REVISIONS	擔當 B Y	檢圖 CHKD	年月日 DATE
△1	-	RE-5-2227	Y.K.G	C.D.H	19.07.24	△					. .
△					. .	△					. .
△					. .	△					. .

THE DIRECTION OF PULLING OUT


● TAPE WIDTH:

24mmMAX






B-B



C-C


REEL DIMENSION (FREE)


THE DIRECTION OF PULLING OUT




● TAPE WIDTH:

32mmMIN





D-D



NOTE 1. 1REEL CONTAINS 500PCS.

HRS DRAWING FOR REFERENCE

NO.	MATERIAL	FINISH,REMARKS	NO.	MATERIAL	FINISH,REMARKS

CODE NO. (OLD)	DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
	LEE 17.06.02 S.G	LEE 17.06.02 S.G	CHO 17.06.02 D.H	SONG 17.06.02 H.C	ENG 19.07.24 DEPT.

SCALE 2:1 / UNITS mm	DRAWING NO. EDC3-632347	PART NO. TF31-**S-0.5SH(895)
	HRS HIROSE KOREA CO.,LTD.	CODE NO CL 6535-0064-8-895

Feb.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

	△数 COUNT	訂正事項 DESCRIPTION OF REVISIONS	擔當 B Y	檢圖 CHKD	年月日 DATE		△数 COUNT	訂正事項 DESCRIPTION OF REVISIONS	擔當 B Y	檢圖 CHKD	年月日 DATE
⚠1	4	RE-5-2227	Y.K.G	C.D.H	19. 07. 24	△					. .
△					. .	△					. .
△					. .	△					. .

●0.5mm PITCH

	PART NUMBER	NUMBER OF CONTACTS	DIMENSION OF CONNECTOR/ FPC, PCB MOUMTING PATTERN									DIMENSION OF PACKING			
			A	B	C	D	E	F	G	H	J	L	M	N	P
	TF31-4S-0.5SH(895)	4S	1.5	2.57	4.7	6.3	3.5	7.3	2.5	3.9	1.75	16	-	6.6	7.5
	TF31-6S-0.5SH(895)	6S	2.5	3.57	5.7	7.3	4.5	8.3	3.5	4.9	1.75	16	-	7.6	7.5
⚠	TF31-7S-0.5SH(895)	7S	3	4.07	6.2	7.8	5	8.8	4	5.4	1.75	16	-	8.1	7.5
	TF31-8S-0.5SH(895)	8S	3.5	4.57	6.7	8.3	5.5	9.3	4.5	5.9	1.75	16	-	8.6	7.5
	TF31-10S-0.5SH(895)	10S	4.5	5.57	7.7	9.3	6.5	10.3	5.5	6.9	1.75	16	-	9.6	7.5
	TF31-12S-0.5SH(895)	12S	5.5	6.57	8.7	10.3	7.5	11.3	6.5	7.9	1.75	24	-	10.6	11.5
	TF31-13S-0.5SH(895)	13S	6	7.07	9.2	10.8	8	11.8	7	8.4	1.75	24	-	11.1	11.5
	TF31-14S-0.5SH(895)	14S	6.5	7.57	9.7	11.3	8.5	12.3	7.5	8.9	1.75	24	-	11.6	11.5
	TF31-16S-0.5SH(895)	16S	7.5	8.57	10.7	12.3	9.5	13.3	8.5	9.9	1.75	24	-	12.6	11.5
	TF31-17S-0.5SH(895)	17S	8	9.07	11.2	12.8	10	13.8	9	10.4	1.75	24	-	13.1	11.5
	TF31-18S-0.5SH(895)	18S	8.5	9.57	11.7	13.3	10.5	14.3	9.5	10.9	1.75	24	-	13.6	11.5
	TF31-20S-0.5SH(895)	20S	9.5	10.57	12.7	14.3	11.5	15.3	10.5	11.9	1.75	24	-	14.6	11.5
	TF31-21S-0.5SH(895)	21S	10	11.07	13.2	14.8	12	15.8	11	12.4	2.0	32	28.4	15.1	14.2
	TF31-22S-0.5SH(895)	22S	10.5	11.57	13.7	15.3	12.5	16.3	11.5	12.9	2.0	32	28.4	15.6	14.2
	TF31-24S-0.5SH(895)	24S	11.5	12.57	14.7	16.3	13.5	17.3	12.5	13.9	2.0	32	28.4	16.6	14.2
⚠	TF31-25S-0.5SH(895)	25S	12	12.57	15.2	16.8	14	17.8	13	14.4	2.0	32	28.4	17.1	14.2
	TF31-26S-0.5SH(895)	26S	12.5	13.57	15.7	17.3	14.5	18.3	13.5	14.9	2.0	32	28.4	17.6	14.2
	TF31-28S-0.5SH(895)	28S	13.5	14.57	16.7	18.3	15.5	19.3	14.5	15.9	2.0	32	28.4	18.6	14.2
	TF31-30S-0.5SH(895)	30S	14.5	15.57	17.7	19.3	16.5	20.3	15.5	16.9	2.0	32	28.4	19.6	14.2
	TF31-32S-0.5SH(895)	32S	15.5	16.57	18.7	20.3	17.5	21.3	16.5	17.9	2.0	32	28.4	20.6	14.2
	TF31-35S-0.5SH(895)	35S	17	18.07	20.2	21.8	19	22.8	18	19.4	2.0	44	40.4	22.1	20.2
	TF31-36S-0.5SH(895)	36S	17.5	18.57	20.7	22.3	19.5	23.3	18.5	19.9	2.0	44	40.4	22.6	20.2
	TF31-40S-0.5SH(895)	40S	19.5	20.57	22.7	24.3	21.5	25.3	20.5	21.9	2.0	44	40.4	24.6	20.2
	TF31-45S-0.5SH(895)	45S	22	23.07	25.2	26.8	24	27.8	23	24.4	2.0	44	40.4	27.1	20.2
	TF31-50S-0.5SH(895)	50S	24.5	25.57	27.7	29.3	26.5	30.3	25.5	26.9	2.0	44	40.4	29.6	20.2
⚠	TF31-53S-0.5SH(895)	53S	26	27.07	29.2	30.8	28	31.8	27	28.4	2.0	44	40.4	31.1	20.2
⚠	TF31-54S-0.5SH(895)	54S	26.5	27.57	29.7	31.3	28.5	32.3	27.5	28.9	2.0	44	40.4	31.6	20.2
	TF31-55S-0.5SH(895)	55S	27	28.07	30.2	31.8	29	32.8	28	29.4	2.0	44	40.4	32.1	20.2
	TF31-60S-0.5SH(895)	60S	29.5	30.57	32.7	34.3	31.5	35.3	30.5	31.9	2.0	56	52.4	34.6	26.2

HRS DRAWING FOR REFERENCE

NO.	MATERIAL	FINISH,REMARKS	NO.	MATERIAL	FINISH,REMARKS

CODE NO. (OLD)	DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
	LEE 17.06.02 S.G	LEE 17.06.02 S.G	CHO 17.06.02 D.H	SONG 17.06.02 H.C	ENG 19.07.24 DEPT.

SCALE 1:1 / UNITS mm	DRAWING NO. EDC3-632347	PART NO. TF31-**S-0.5SH(895)
	HRS HIROSE KOREA CO.,LTD.	CODE NO CL 6535-0064-8-895 3/5

Feb.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

This connector requires dslicate and careful handing.
Read through the instructions shown below and the connector properly.
Each values indicating here are for reference and may differ from standard value.


[INSTRUCTIONS FOR MOUNTING ON THE BOARD]

◆ Warp of Board
Minmize warp of the board as possible
Lead co-planarity including reinforced metal fitting is 0.1mm or less
Too much warp of the board may result in a soldering.

◆ Load to Connector
Do not apply a force of 0.5N or more to the connector before mounting it on the board.
Otherwise, the connector may be broken.
Do not warp the FPC or operate the connector before mounting it.

◆ Load to board
°Splitting a large board into seveal pieces
°Screwing the board
Avoid the handling described above so that no force is exerted on the board during the assembly process.
Otherwise, the connector may become defective.


◆ Amount of Warp
The warp of a 100-mmwide board should be 0.5mm or less.
The warp of board suffers stress on connector and connector may become defective.




HRS DRAWING FOR REFERENCE

[INSTRUCTIONS ON INSERTING FFC/FPC AND CONNECTOR]


◆ Use of the Actuator
1. Be very careful not to apply excessive force when releasing the Actuator.
in the initial position
if you use your nail or finger as shown, the terimals may be deformed.



2. The actuator rotates around the rotational axis as shown below.
Rotate the actuator.
3. The actuator will not open more than 110°.
Do not apply any force backward beyond this point.
Otherwise the actuator may come off or braek.



4. Move the actuator at approximately the center.
5. Do not pinch or pick the actuator to lift it as shown below. Otherwise it may break.
(Do not carry out any operation other than rotating the actuator as shown in 2 above.)



<INSTRUCTION MANUAL(1)>

DRAWING NO.	PART NO. TF31-**S-0.5SH(895)	
HRS HIROSE KOREA CO.,LTD.	CODE NO. CL 6535-0064-8-895	4/5


Feb.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


◆Direction of Contacts

This connector has contacts on the bottom. Thus, insert FFC/FPC with the exposed conductors face down.

◆Inserting the FFC/FPC

1. Insert the FFC/FPC by about 10 degrees along the surface and at a right angle to the connector.
   Insert it properly to the very end.





Right angle to the connector

2. Do not insert the FFC/FPC diagonally from above.

If the FFC/FPC is inserted at a slant (incorrectly) as shown below inthe FFC/FPC insertion process.
the edge of the FFC/FPC may catch in the terminals resulting in deformation of the terminals.
the FFC/FPC may bend and patterns may break or the FFC may not insert completely.
resulting in improper conduction.


※ Keep a sufficient FPC/FFC insertion space in the stage of the layout in order to avoid incorrent FPC/FFC insertion.
Besides, it is not difficult to insert FFC/FPC correctly all the way to the end.
Design the proper layout of parts.

※ Make adjustments with the FFC/FPC manufacturer for bending perfomance and breakage.



3. Do not rotate the actuator when FFC/FPC TAB is on right and left guides for positioning FFC/FPC.

Make sure the position of FFC/FPC TAB and guides before rotate the actuator.



◆Checking the Locking Condition


In the locked condition make sure that the actuator is horizontal on the board surface.
Do not apply excessive force to it near the 0° position of the actuator.
Otherwise the terminals may be deformed.

[INSTRUCTION ON FFC/FPC LAYOUT AFTER CONNECTOR]

◆Load to FFC/FPC

Be very careful not to apply any force to the connector directly after inserting FFC/FPC.
Otherwise the connector may become unlocked or the FFC/FPC may break.
In particular design the FFC/FPC layout with care not to bend it sharply upward in a vertical direction near the insertion opening.
Fix the FFC/FPC when loads are applied to it continuously.

Load: 0.1 x n N MAX
(n: number of contacts)




HRS DRAWING FOR REFERENCE

[INSTRUCTIONS ON REMOVING FPC]

◆Move the actuator at approximately the center.

◆Release the actuator to remove the FFC/FPC.

Remove the FFC/FPC by about 10drgrees along the surface.



[OTHER INSTRUCTIONS]

◆Instruction on Manual Soldering

Follow the instructions shown when soldering the connector manually during repair work,etc.
1. Do not perform reflow soldering or manual soldering with the FFC/FPC inserted into the connector.
2. Do not heat the connector excessively. Be very careful not to let the soldering iron contact any parts other than connector leads. Otherwise, the connector may be deformed or melt.
3. Do not use excessive solder(or flux)
   if excessive solder(or flux) is used on the terminals, solder or flux may adhere to the contacts or rotating parts of the Actuator, resulting in poor contact or a rotation failure of the Actuator.
   Supplying excessive solder to the reinforcing bracket may lock hinder Actuator.
   resulting in breakage of the connector.

<INSTRUCTION MANUAL(2)>

DRAWING NO.	PART NO. TF31-**S-0.5SH(895)	
HRS HIROSE KOREA CO.,LTD.	CODE NO. CL 6535-0064-8-895	5/5