







May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.




- NOTE
- 1 . ALL LEAD CO-PLANARITY SHALL BE 0.08mm MAX.
 - 2 CONTACT PLATING SPECIFICATIONS
CONTACT AREA : GOLD 0.05 μ m MIN
SMT LEAD : GOLD 0.05 μ m MIN
UNDERPLATING : NICKEL 1 μ m MIN
(SURFACE : SEALING)
 - 3 CAV NO. ARE INDICATED IN APPROX POSITION SHOWN.

	COUNT	DESCRIPTION OF REVISIONS	B	Y	CHKD	DATE		COUNT	DESCRIPTION OF REVISIONS	B	Y	CHKD	DATE
△	-	RE-6-2476			PSH	JHW	21. 11. 08	△					
△								△					
△								△					

ENGAGEMENT FIGURE (50:1)




SIGNAL CONTACT




POWER CONTACT

4	PS	CLEAR (EMBOSSED CARRIER TAPE)							
3	COPPER ALLOY	2							
2	COPPER ALLOY	2							
1	LCP	UL94 V-0, BLACK							
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS				
REMARKS				DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED	
				S. H. PARK	S. H. PARK	H. W. JO	H. W. JO	21. 04. 12	
				21. 04. 12	21. 04. 12	21. 04. 12	21. 04. 12		
CODE NO. (OLD)	SCALE	DRAWING NO.	PART NO.						
	10:1	EDC3-633348-80	BK13C06-6DS/2-0.35V(800)						
	UNITS	HIROSE KOREA CO., LTD.	CODE NO		CL 6665-0051-6-800				1/3
	mm								


5 RECOMMENDED PCB LAYOUT



RECOMMENDED METAL MASK DIMENSIONS
METAL MASK THICKNESS : $80 \mu\text{m}$



4 RECOMMENDED REFLOW TEMPERATURE PROFILE
USING LEAD-FREE SOLDER PASTE.



REFLOW METHOD : N_2 REFLOW
NUMBER OF REFLOW CYCLES : 2 CYCLES MAX.
1) REFLOW TIME
DURATION ABOVE 220°C, 60 SEC MAX.
(PEAK TEMPERATURE : 250°C MAX)
2) PRE-HEAT TIME
PRE-HEAT TEMPERATURE(MIN): 150°C
PRE-HEAT TEMPERATURE(MAX): 180°C
PRE-HEAT TIME: 90-120 SEC.


4. THIS TEMPERATURE PROFILE IS PER THE CONDITIONS SHOWN ABOVE. ADDITIONAL FACTORS SUCH AS SOLDER PASTE TYPE, PCB SIZE AND OTHER MOUNTED COMPONENTS COULD AFFECT THE PROFILE. THEREFORE, A THOROUGH EVALUATION OF MOUNTING CONDITION IS REQUIRED PRIOR TO PRODUCTION. TEMPERATURE IS MEASURED AT CONTACT LEAD.

5. PLEASE CONTACT US IN CASE YOU WILL MAKE DIFFERENT SETTINGS FROM OUR RECOMMENDATION.
6. THIS PRODUCT SATISFIES HALOGEN FREE REQUIREMENTS DEFINED AS 900ppm MAXIMUM CHLORINE, 900ppm MAXIMUM BROMINE, AND 1500ppm MAXIMUM TOTAL OF CHLORINE AND BROMINE.
7. THIS PRODUCT COMPLY WITH RoHS.


	DRAWING NO.	EDC3-633348-80	PART NO.	BK13C06-6DS/2-0.35V(800)
	SCALE	10:1	CODE NO	CL 6665-0051-6-800
	UNITS	mm		

May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


EMBOSSED CARRIER TAPE PACKAGING (5:1)




D-D (5:1)



C-C (5:1)




DIRECTION OF UNREELING




10 TAPING(FREE)

STYLE AND DIMENSION OF REEL (FREE)



E (10:1)



DETAIL OF PART No. LABEL

SUPPLIER	
QUANTITY	
PART NO.	
CODE NO.	
DATE OF MANUFACTURED	
生産月日	年 月 日
図番	** ** *
品名	BK13C06-6DS/2-0.35V(800)
納入数量	20,000個
納入者	HIROSE KOREA

8 . PER REEL 20,000 CONNECTORS.

9 . THE DIMENSIONS IN PARENTHESES ARE FOR REFERENCE.

10 REFER TO JIS C 0806, IEC-60286-3 (PACKAGING OF COMPONENTS FOR AUTOMATIC HANDLING)

DRAWING NO.	EDC3-633348-80	PART NO.	BK13C06-6DS/2-0.35V(800)
SCALE	10:1	CODE NO	CL 6665-0051-6-800
UNITS	mm		
	HIROSE KOREA CO., LTD.		