

Mar.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
① 10	RE-6-2403	LCE	JHW	21.09.13	③ 1	RE-6-3975	SJH	JHW	25.01.20
② 2	RE-6-2541	LCE	JHW	21.12.27					

APPLICABLE STANDARD

RATING	OPERATING TEMPERATURE RANGE	-55℃ TO +85℃(note1)	STORAGE TEMPERATURE RANGE	-10℃ TO +60℃
	VOLTAGE	③ ② 50 V AC/DC	APPLICABLE CONNECTOR	BK22C07-4DS/2-0.4V(***)
	CURRENT	SIGNAL CONTACT 0.3A POWER CONTACT 15.0A		

SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
------	-------------	--------------	----	----

CONSTRUCTION

GENERAL EXAMINATION	CONFIRMED VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X
MARKING	CONFIRMED VISUALLY.		X	X

ELECTRICAL CHARACTERISTICS

CONTACT RESISTANCE	20mV AC OR LESS 1kHz, 1mA	SIGNAL CONTACT : 30mΩ MAX ① POWER CONTACT : 5mΩ MAX ①	X	-
INSULATION RESISTANCE	100V DC	50MΩ MIN	X	-
VOLTAGE PROOF	150V AC FOR 1min. ②	NO FLASHOVER OR BREAKDOWN	X	-

MECHANICAL CHARACTERISTICS

MECHANICAL OPERATION	10 TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE: SIGNAL CONTACT : 30mΩ MAX ① POWER CONTACT : 5mΩ MAX ① ② NO DAMAGE, CRACK OR LOOSENESS OF PATRS.	X	-
VIBRATION	FREQUENCY 10 TO 55 TO 10 Hz, APPROX 5min SINGLE AMPLITUDE 0.75mm, 10CYCLES, FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-
SHOCK	490 m/s² DURATION OF PULSE 11ms AT 3 TIMES FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-

ENVIRONMENTAL CHARACTERISTICS

RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55 → +85℃ TIME 30 → 30 min UNDER 5 CYCLES. (RELOCATION TIME TO CHAMBER: WITHIN2~3 MIN)	① CONTACT RESISTANCE: SIGNAL CONTACT : 30mΩ MAX ① POWER CONTACT : 5mΩ MAX ① ② INSULATION RESISTANCE: 50MΩ MIN ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-
DAMP HEAT (STEADY STATE)	EXPOSED AT 40±2℃, 90 TO 95%, 96h.	① CONTACT RESISTANCE: SIGNAL CONTACT : 30mΩ MAX ① POWER CONTACT : 5mΩ MAX ① ② INSULATION RESISTANCE: 25MΩ MIN ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-
SULPHUR DIOXIDE	EXPOSED IN 25 PPM FOR 96h, 25℃, 75±5%RH. (Test standard : JIS C 60068)	① CONTACT RESISTANCE: SIGNAL CONTACT : 30mΩ MAX ① POWER CONTACT : 5mΩ MAX ① ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-

REMARKS Note 1 : INCLUDE THE TEMPERATURE RISING BY CURRENT.	DRAWN D.K.YUN	DESIGNED D.K.YUN	CHECKED S.Sunaga	APPROVED H.W.JO	RELEASED ENG 25.01.20 DEPT
Unless otherwise specified, refer to JIS C 5402 and IEC 60512	20.12.29	20.12.29	20.12.29	20.12.29	

Note QT: QUALIFICATION TEST AT: ASSURANCE TEST X: APPLICABLE TEST

HIROSE KOREA CO.,LTD.	SPECIFICATION SHEET	PART NO. BK22C07-4DP/2-0.4V(800)
-----------------------	---------------------	-------------------------------------

CODE NO.(OLD)	DRAWING NO. ELC3-633241-08	CODE NO. CL 6677-0001-8-800	1/1
---------------	-------------------------------	--------------------------------	-----